



LOW-PRESSURE MANOMETER

WITH 1.999 inH₂O LOW RANGE

10.04 inH₂O HIGH RANGE

HHP-103
\$579



HHP-103, \$579, shown actual size.

- ✓ Measure Differential Gage or Vacuum
- ✓ Auto-Ranging Display
- ✓ One-Handed Operation
- ✓ Rugged, Water-Resistant Case

The HHP-103 handheld manometer is designed for one-handed industrial or laboratory use. The custom-molded case allows heavy use in humid environments. A high-contrast LCD with backlight enables easy reading.

The HHP-103 can measure gage, vacuum, or differential pressures by venting the low and high ports to atmosphere. For greater precision, it offers both a low and high range.

SPECIFICATIONS

Accuracy: 0.2% FS of high range

Operating Temperature: -10 to 50°C (14 to 122°F)

Compatible Media: Dry, non-corrosive gases

Power: 9V battery included (approx 300-hr operation)

Zero Adjustment: Front-panel button
Display: 3½ digit, 13 mm (0.5"), backlight

Pressure Port: Tube fitting for 0.155" < ID > 0.195", OD < 0.24" Tygon® or silicon tubing (tubing not included)

Dimensions: 140 H x 70 W x 26 mm D (5.50 x 2.75 x 1.00")

Weight: 250 g (8.8 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)			
MODEL NO.	PRICE	RANGE	
		LOW	HIGH
AUTO-RANGING, PUSHBUTTON-SELECTABLE ENGINEERING UNITS			
HHP-103	\$579	0 to 1.999 inH ₂ O	0 to 10.04 inH ₂ O

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
OS200-COVER	\$41	Protective rubber boot
TYTY-732532-50	40	15.2 m (50') Tygon tubing
ME-1805	131	Reference Book: Instrumentation Fundamentals

Comes complete with 9V battery and operator's manual.

Ordering Example: HHP-103, auto-ranging air pressure meter with pushbutton-selectable engineering units and 0 to 1.999 inH₂O low-range and 0 to 10.04 inH₂O high range, OS200-COVER, protective rubber boot, and TYTY-732532-50, 15.2 m (50') of Tygon tubing, \$579 + 41 + 40 = \$660.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters