

ECONOMICAL, HANDHELD DIGITAL MANOMETER

0 to 50 inH₂O (0 to 1.9 psi)

HHP-90
\$302

- ✓ 7 Selectable Pressure Scales
- ✓ Differential Input with 8 mm (5/16") Tube Connectors
- ✓ Water Resistant, IP67 Rated
- ✓ Rugged Case with Protective Rubber Boot
- ✓ Magnetic Attachment or Tilt Stand
- ✓ Backlit Digital Display
- ✓ Pushbutton Zero and Hold Features
- ✓ Auto Power-Off after 12 Minutes

OMEGA's HHP-90 is a rugged handheld manometer featuring high accuracy and resolution, fast response time, and selectable engineering units—all at a low cost.

Made of ABS plastic, the HHP-90 is water resistant and comes with a protective rubber boot. Additional features include a built-in tilt stand and magnetic mount and a backlit LCD, which is easy to see even in poor light.

SPECIFICATIONS

Accuracy at -10 to 50°C (14 to 122°F): ±0.2% of rdg + 0.2% FS + 1 LSD

Operating Temp: -10 to 50°C (14 to 122°F)

Compatible Media: Dry, non-corrosive gases

Power: 2 "AA" batteries (included)

Battery Life: 200 hours; low-battery indicator on display

Units: inH₂O, mmH₂O, mbar, psi, kPa, inHg and mmHg

Pressure Ports: Tube connectors for 8 mm (5/16") ID flexible tubing

Safe Over Range: 1 bar (14.5 psi)

Dimensions: 155 H x 67 W x 40 mm D (6.1 x 2.6 x 1.6")

Weight: 180 g (6.4 oz) without protective boot

RANGES & RESOLUTION		
UNITS	LOW RANGE	HIGH RANGE
inH ₂ O	—	0 to 52.28
mmH ₂ O	0 to 199.9	0 to 1320
mbar	0 to 19.99	0 to 130
psi	—	0 to 1.88
kPa	—	0 to 13
inHg	—	0 to 3.83
mmHg	0 to 19.99	0 to 97.5



HHP-90, \$302, comes with batteries, rubber boot, tilt stand and magnetic mount, and complete operator's manual, shown smaller than actual size. Tubing not included.

A


PRESSURE INSTRUMENTS

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
HHP-90	\$302	Handheld digital manometer with rubber boot and magnetic mount

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
TYVY-12516-100	\$45	30.4 m (100') of vinyl tubing, 1/2" OD x 5/16" ID
ES-2199	99	Reference Book: Handbook of Air Pollution Control 

Comes complete with 2 "AA" batteries, rubber boot, tilt stand and magnetic mount, and operator's manual. Tubing not included, visit omega.com/tyvy for additional tubing information.

Ordering Example: HHP-90, handheld digital manometer, and TYVY-12516-100, 30.4 m (100') spool of vinyl tubing, \$302 + 45 = \$347.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters