

PLUG-IN PRESSURE MODULES FOR PCL-1B AND PCL-2A CALIBRATORS

PCL-M Series

- ✓ Gage, Absolute, Vacuum, Compound and Differential Models
- ✓ Accurate Up to 0.06% of Span
- ✓ Ranges Available from 0.25 inH₂O to 7500 psi

Plug-in pressure modules allow range changes without calibration, shown smaller than actual size. Modules sold separately, see ordering chart below.



Works With Both
PCL-1B and PCL-2B

PCL-1B, shown smaller than actual size, visit omega.com/pcl-1b



To Order Visit omega.com/pcl-m for Pricing and Details

PLUG-IN PRESSURE MODULES

UNI-DIRECTIONAL

MODEL NO.	RANGE (inH ₂ O)
PCL-MA-0.25WC	0 to 0.25
PCL-MA-0.5WC	0 to 0.5
PCL-MA-01WC	0 to 1.0
PCL-MA-02WC	0 to 2.0
PCL-MA-03WC	0 to 3.0
PCL-MA-05WC	0 to 5.0
PCL-MA-10WC	0 to 10
PCL-MA-15WC	0 to 15
PCL-MA-25WC	0 to 25
PCL-MA-50WC	0 to 50
PCL-MA-100WC	0 to 100
PCL-MA-150WC	0 to 150
PCL-MA-200WC	0 to 200

BI-DIRECTIONAL

PCL-MA-0.125BWC	±0.125
PCL-MA-0.25BWC	±0.25
PCL-MA-0.5BWC	±0.5
PCL-MA-01BWC	±1.0
PCL-MA-1.5BWC	±1.5
PCL-MA-2.5BWC	±2.5
PCL-MA-05BWC	±5.0
PCL-MA-7.5BWC	±7.5
PCL-MA-12.5BWC	±12.5
PCL-MA-25BWC	±25
PCL-MA-50BWC	±50
PCL-MA-100BWC	±100

To Order Visit omega.com/pcl-m for Pricing and Details

PLUG-IN PRESSURE MODULES

GAGE PRESSURE

MODEL NO.	RANGE (psig)
PCL-MB-005G	0 to 5
PCL-MB-010G	0 to 10
PCL-MB-015G	0 to 15
PCL-MB-020G	0 to 20
PCL-MB-030G	0 to 30
PCL-MB-050G	0 to 50
PCL-MB-100G	0 to 100
PCL-MB-250G	0 to 250
PCL-MB-300G	0 to 300
PCL-MB-500G	0 to 500
PCL-MB-600G	0 to 600
PCL-MB-1KG	0 to 1000
PCL-MB-1.5KG	0 to 1500
PCL-MB-2KG	0 to 2000
PCL-MB-2.5KG	0 to 2500
PCL-MB-3KG	0 to 3000
PCL-MB-5KG	0 to 5000
PCL-MB-6KG	0 to 6000
PCL-MB-7.5KG	0 to 7500

COMPOUND RANGES

PCL-MB-05BG	±5
PCL-MB-010BG	±10
PCL-MB-15V30BG	-15 to 30
PCL-MB-15V60BG	-15 to 60

VACUUM RANGES

PCL-MB-05VG	0 to -5
PCL-MB-10VG	0 to -10
PCL-MB-15VG	0 to -15



PCL-2A, \$2200, shown smaller than actual size, visit omega.com/pcl-2a

To Order Visit omega.com/pcl-m for Pricing and Details

ABSOLUTE PRESSURE MODULES

MODEL NO.	RANGE (psia)
PCL-MB-005A	0 to 5
PCL-MB-010A	0 to 10
PCL-MB-015A	0 to 15
PCL-MB-020A	0 to 20
PCL-MB-030A	0 to 30
PCL-MB-050A	0 to 50
PCL-MB-100A	0 to 100
PCL-MB-250A	0 to 250
PCL-MB-300A	0 to 300
PCL-MB-500A	0 to 500
PCL-MB-1KA	0 to 1000
PCL-MB-1.5KA	0 to 1500
PCL-MB-2KA	0 to 2000
PCL-MB-2.5KA	0 to 2500
PCL-MB-3KA	0 to 3000
PCL-MB-5KA	0 to 5000
PCL-MB-6KA	0 to 6000
PCL-MB-7.5KA	0 to 7500

Note: Pressure modules are interchangeable with calibrator models PCL-1B and PCL-2A, visit omega.com for details.

Ordering Examples: PCL-MB-050A, 0 to 50 psia pressure module.

PCL-MB-05BG, compound ±5 psig range pressure module.