

# SOLID STATE SWITCHES FOR HIGH-CYCLE APPLICATIONS

**PSW601 Series**  
30 to 20,000 psi  
Watertight Enclosure NEMA 4 (IP65)

Starts at  
**\$410**



See switch accessories on page H-47 for audible alarms and relay modules.



- ✓ Watertight, Corrosion-Resistant Case
- ✓ Thin-Film Sensor for Long, Stable Life—Minimum 1 Million Cycles at Rated Load
- ✓ Reliable in Industrial Environments
- ✓ Field Adjustable

OMEGA's PSW601 Series switches are designed to provide long, stable life. They use a thin-film sensor with a minimum life of 1 million cycles. Solid state circuitry analyzes the signal from the sensor to activate the switch at the setpoint. Deadbands are adjustable from 0.1 to 95% of range, and status lights give a visual indication of switch status.

## SPECIFICATIONS

**Switch:** UL- and CSA-rated SPDT switch

**Electrical:** 10 A, 125/250 Vac resistive and inductive; 10 A, 30 Vdc resistive

**Temperature Limits:**  
-29 to 71°C (-20 to 160°F)

**Temperature Effects:** 2% FS/25°C

**Repeatability:** ±0.5% full range

**Proof Pressure:** See "To Order" chart

**Deadband:** Adjustable 0.1 to 95% of range

**Power Requirements:**

**Standard:** 24 Vdc, 12 mA unactivated; 43 mA activated

**Optional:** 110 to 120 Vac 50/60 Hz or 250 Vac 50/60 Hz

**Enclosure:** Anodized aluminum body; watertight, NEMA 4 (IP65)

**Process Connection:**

≤7500 psi: ¼ FNPT  
>7500 psi: ¼ Amino-F

**Electrical Connections:** ½ NPT conduit fitting with #18 AWG 450 mm (18") insulated wire leads

**Wetted Parts:** 316 SS fitting and 17-4 PH SS diaphragm

**Dimensions:** 144 H x 102 W x 59 mm D (5.7 x 4 x 2.3")

**MOST POPULAR MODELS HIGHLIGHTED!**

## To Order (Specify Model Number)

SETPOINT LIMITS (psi)	MODEL NUMBER	PRICE	PROOF (psi)	BURST (psi)
<b>STANDARD MODELS: 24 Vdc, SINGLE 10 A Switch</b>				
3 to 30	PSW601B-30	\$410	120	480
3 to 60	PSW601B-60	410	120	480
5 to 100	PSW601B-100	410	200	800
10 to 200	PSW601B-200	410	400	1600
15 to 300	PSW601B-300	410	600	2400
25 to 500	PSW601B-500	410	1000	4000
35 to 750	PSW601B-750	410	1500	6000
50 to 1000	PSW601B-1K	410	2000	8000
100 to 2000	PSW601B-2K	410	4000	16,000
150 to 3000	PSW601B-3K	410	4500	9000
250 to 5000	PSW601B-5K	410	7500	15,000
375 to 7500	PSW601B-7.5K	410	9000	11,250
500 to 10,000	PSW601A-10K*	410	12,000	15,000
750 to 15,000	PSW601A-15K*	410	18,000	22,000
1000 to 20,000	PSW601A-20K*	410	24,000	30,000

\* Process connection is a ¼" Amino-F fitting. Comes with complete operator's manual.

For 110 Vac powered models, add suffix "-110VAC" to model number; no extra charge. For 250 Vac powered models, add suffix "-250VAC" to model number; add \$50 to price.

**Ordering Example:** PSW601B-100, 24 Vdc power, range of 5 to 100 psi and single 10 A switch, \$410.

## ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4391	\$120	Reference Book: Centrifugal Pump Design



PSW601B-5K, \$410, shown smaller than actual size.



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters