

ECONOMICAL BAROMETRIC PRESSURE TRANSDUCER

PX2760 Series

All Models
\$395



- ✓ Rugged Capacitive Design
- ✓ Excellent Long-Term Stability
- ✓ Fast Response Time
- ✓ Small Size
- ✓ Integral Mounting Bracket
- ✓ Instant Warm-Up

OMEGA's PX2760 Series barometric pressure transducers use a capacitive sensor that has excellent thermal stability and low hysteresis. The signal is processed through a custom ASIC, ensuring long-term reliability and accuracy. The amplified 0.1 to 5.1 Vdc output makes these transducers compatible with most process controllers and computer interface equipment and is virtually immune to EMI and RFI.

SPECIFICATIONS

Excitation: 12 Vdc (9 to 14.5 Vdc max)

Power Consumption: <0.2 W

Output Impedance: <5 Ω

Output: 0.1 to 5.1 Vdc, 3-wire

Accuracy: ±0.25% span RSS at constant temperature (includes linearity, repeatability and hysteresis)

Resolution: Infinite, limited only by noise level (0.005% FS)

Response Time: <10 ms to reach 90%

Long-Term Stability: ±0.25% FS over 6 months @ 70°F

Operating Temperature Range: -20 to 80°C (-4 to 176°F)

Compensated Temperature Range: 0 to 55°C (32 to 131°F)

Storage Temperature: -55 to 120°C (-67 to 248°F)

Thermal Zero Effect: ±0.01%/°F span

Thermal Span Effect: ±0.01%/°F span

PX2760-600A5V, \$395, shown smaller than actual size.



Pressure Ratings:

Range	Max Pressure
600 to 1100 mbar (450 to 825 mmHg)	20 psia
800 to 1100 mbar (600 to 825 mmHg)	20 psia
0 to 20 (0 to 1034 mmHg)	30 psia

Sensor: Capacitive

Shock: 50 g operating, 1/2 sine 10 ms

Vibration: 2 g from 5 to 500 Hz


Acceleration: 10 g maximum

Media: Dry or non-condensing gases compatible with wetted parts

Wetted Parts: Stainless steel, alumina, gold and elastomer

Pressure Port: 1/8" tube fitting

Electrical Connection: 0.6 m (2') cable



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

RANGE (Absolute Pres)	MODEL NO.	PRICE	COMPATIBLE METERS
600 to 1100 mbar	PX2760-600A5V	\$395	DP41-E, DP25B-E, DP-3002E
800 to 1100 mbar	PX2760-800A5V	395	DP41-E, DP25B-E, DP-3002E
0 to 20 psia	PX2760-20A5V	395	DP41-E, DP25B-E, DP-3002E

All models come complete with operator's manual.

Ordering Example: PX2760-600A5V, barometric range pressure transducer, 600 to 1100 mbar absolute, with voltage output, \$395.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ES-2160	\$125	Reference Book: Air Quality Compliance



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters