





# EXTRUDER RTD PROBES WITH BAYONET FITTINGS

- Ideal for Plastic Process Machinery
- Precision 100 Ω Class "B" Thin Film DIN Platinum Element
- Bayonet Locking Cap and Spring Lock Sensor into Bayonet Style Port (Threaded Fittings Available)
- 4.75 mm (3/16") Diameter, 304 Stainless Steel Sheath Standard
- 1.5 m (60") Flex Cable Standard
- 3-Wire Construction Color Coded Red/Red/White Per IE/ASTM-E-230
- Temperature Range to 260°C (500°F) Continuous [Optional 480°C (900°F) Cable Available]



**BTTF Series Starts at £39**




## To Order (Specify Model Number)

## MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.*	TERMINATION	BEND	"A" DIM** mm (in)	PRICE
BTTF-000-RTD-2-1/4-60-1	Spade Lugs	Straight	60 (2.36)	£39
BTTF-000-RTD-2-1/4-60-2	OTP Connector	Straight	60 (2.36)	42
BTTF-000-RTD-3-1/2-60-1	Spade Lugs	Straight	90 (3.54)	39
BTTF-000-RTD-3-1/2-60-2	OTP Connector	Straight	90 (3.54)	42
BTTF-090-RTD-2-1/4-60-1	Spade Lugs	90°	60 (2.36)	39
BTTF-090-RTD-2-1/4-60-2	OTP Connector	90°	60 (2.36)	42
BTTF-090-RTD-3-1/2-60-1	Spade Lugs	90°	90 (3.54)	39
BTTF-090-RTD-3-1/2-60-2	OTP Connector	90°	90 (3.54)	42

Adaptors for insertion and pipe clamp use also available; see page A-154 for complete information. \*For other lengths of armoured cable, change "-60" in model number to length desired and add £2.30 per foot over 5' (60"). \*\*Other A lengths available. Price £3.40 + £0.65p per inch over 6".  
**Ordering Examples:** BTTF-090-RTD-3 1/2-120-1, 90-degree bend probe, 3 1/2" long dimension "A", 120" of flexible armour cable, add a spade lug termination, £39 + 3.40 x 3.50 = £45.90.




## To Order (Specify Model Number)

## MOST POPULAR MODEL HIGHLIGHTED!

	LENGTH (in)	THREAD SIZE	PRICE
BTA-1	7/8	1/2-27 NPT	£4
BTA-2	7/8	3/8-24	4
BTA-3	1 1/8	1/2-27 NPT	4.70
BTA-4	1 1/8	3/8-24	4.70
BTA-5	2 1/8	1/2-27 NPT	5.40
BTA-6	2 1/8	3/8-24	5.40

## HOW ARE OMEGA'S MODEL NUMBERS CONSTRUCTED?



Ordering Example: BTTF-090-RTD-2-1/4-60-1, spade lugs, £39.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters