



# Fine Diameter 1.5 mm RTD Probes


Starts at  
**£49**

**OMEGACAL™**  
Factory CAL  
AVAILABLE  
[omega.co.uk](http://omega.co.uk)

MADE IN  
**UK**

**ACCURACY**  
IEC CLASS **A**  
(±0.15°C @ 0°C)

Also Available!  
PFA Coating—  
Consult Sales



- ✓ 100 DIN Platinum Class “A” Per IEC 60751
- ✓ OMEGA’s Platinum RTD Probes Are Now Available in 1.5 mm Diameter for Faster Response Times

PR-17 Series quick disconnect probe with miniature size connector, £53.25 (includes mating connector).

**Note:** Because of their smaller physical size, these probes are more fragile and should be handled with greater care than our larger diameter versions of the same probes. Avoid subjecting probes to bending, flexing or vibration.

PR-11 Series Transition junction probe with 1 m PFA insulated leads, strip end termination standard, £49.

Add a Connector!  
Add Suffix “-MTP” for miniature or “-OTP” for standard size connector, and add £4.70.

PR-16 Series utility handle probe, £64.

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model Number	Lead Style <sup>†</sup>	Ohms @ 0°C	**Sheath Length			
			150 mm	300 mm	450 mm	600 mm
PR-11-2-M15-(*)	2	100	£49.00	£50.00	£52.00	£53.00
PR-16-2-M15-(*)	2	100	64.00	66.00	67.00	68.00
PR-17-2-M15-(*)	2	100	53.25	54.75	56.25	57.75

<sup>†</sup> Available in lead type 2 (3-wire) and lead type 1 (2-wire); please see [omega.co.uk](http://omega.co.uk). Please contact Custom Engineering for 4-wire, type 3.

\* Specify sheath length. Minimum sheath length for any style probe is 100 mm. 1.5 mm dia RTD probes cannot be bent. For intermediate lengths, use next longer probe price. Over 600 mm, consult Sales. Actual diameter of sheath is 1.5 mm ± 0.075 mm. To order additional lead length on the PR-11 style probes, consult Sales Department. European curve a = 0.00385.

\*\* Intermediate probe lengths are available at the price of next longer standard probe. Longer probes are available through Custom Engineering.

**Ordering Example:** PR-17-2-M15-150, quick disconnect probe 150 mm long, lead type 2 (3-wire configuration), 1.5 mm dia., 304 SS sheath, **£53.25**.



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters