

# OMEGAMETER™ Mix and Match Series Digital Multimeters with Non-Contact Voltage Audible Buzzer Feature



HHM33 **£19<sup>50</sup>**




**3½ digit, 1999 Counts Digital Display**  
**DC Volts:** 0 to 2 V/20 V/600 V ±1.2%  
**AC Volts:** 0 to 200 V/600 V/50 to 500 Hz ±2.5%  
**DC Current:** 0 to 200 µA/2 mA/20 mA/200 mA/10 A ±2.5%  
**Resistance:** 0 to 200 Ω/2 KΩ/20 KΩ/200 KΩ/20 MΩ ±2.0%  
**Resolution:** 1 mV, 100 mV, 0.1 µA, 0.1 Ω  
**Battery Test:** 1.5 V/9 V ±3.5%  
**Diode Test**  
**10A Fused**  
**Safety Input Sockets**  
**Safety Test Leads**  
**Overload Protection on All Ranges**



Test leads included with all models shown!

**Special Non-Contact Voltage Feature: Meter Buzzes when Placed Near Live Electrical Circuits.**



HHM34 **£26**

**3½ digit, 1999 Counts Digital Display**  
**DC Volts:** 0 to 200 mV/2 V/20 V/600 V ±1.2%  
**AC Volts:** 0 to 200 mV/2 V/200 V/600 V/50 to 500 Hz ±2.0%  
**DC Current:** 0 to 200 µA/20 mA/200 mA/10 A ±1.5%  
**AC Current:** 0 to 200 µA/20 mA/200 mA/10 A/50 to 500 Hz ±2.0%  
**Resistance:** 0-200 Ω/2 KΩ/200 KΩ/20 MΩ ±1.5%  
**Resolution:** 100 µV, 0.1 µA, 0.1 Ω  
**Diode Test**  
**Continuity Test**  
**Non-Contact Voltage Indicator**  
 Low-tension lines from 70 to 440Vac 50 to 60 Hz  
**Data Hold, MAX Hold, 10A Fused, Safety Input Sockets, Safety Test Leads**  
**Overload Protection on All Ranges**



HHM35 **£33**

**3200 Counts with Annunciators**  
**Auto Power-Off Function**  
**Auto or Manual Range Selection**  
**Bar Graph Display:** 12 time/sec sampling  
**DC Volts(Auto):** 0 to 320 mV/3.2 V/32 V/320 V/600 V ±1.2%  
**AC Volts(Auto):** 0 to 3.2 V/32 V/320 V/600 V/ 50-200 Hz ±2.0%  
**DC Current:** 0 to 320 µA/3200 µA/32 mA/320 mA/10 A ±2.0%  
**AC Current:** 0 to 320 µA/3200 µA/32 mA/320 mA/10 A ±2.5%  
**Resistance:** 0 to 320 Ω/3.2 KΩ/320 KΩ/3.2 MΩ/30 MΩ ±1.5%  
**Resolution:** 100 µV, 0.1 µA, 0.1 Ω  
**Diode Test**  
**Continuity Test, Data Hold, 10A Fused, Safety Input Sockets, Safety Test Leads, Overload Protection on All Ranges**

**CHEAPER BY THE DOZEN!**  
 Purchase any Combination of 12 Units and Save 20%

All models shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price*	Description
HHM33	£19.50	Basic DMM
HHM34	26.00	Voltage DMM with non-contact feature
HHM35	33.00	Multifunction DMM
HHM-TL	3.40	Spare set of test leads
HHM-CAL	37.00	Calibration certificate

\* Buy any combination of 12 units at one time and save 20%.

Comes with test leads and operator's manual.

Ordering Example: HHM35, multifunction DMM and HHM-TL, spare set of test leads, £33 + 3.40 = £36.40.



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters