

ENCLOSURE DOOR LATCH ACCESSORIES


HANDLES, KNOBS AND KEY LATCHES

SCE Series

- Increase Security with Key Locking or Pad Locking
- Choose From Chrome or Black Finish
- Create Easy Access with Wing Knob Latches
- Three-Point Latch Kit for Enviroline® Series
- Non-Locking Key Designs Available

Door latch inserts are designed for increased security and access. They are designed for a quick and easy conversion from the standard quarter turn latch, or mini quarter turn latch, with no added holes or cutouts necessary for installation. Choose from key locking or padlocking latches for added security or wing knob latches for easy access.

The three-point latch kit is designed for use with all Enviroline Series enclosures 42" or higher. This latch kit will add a two or three point latching system to the enclosures with easy to cut and install rod guides and $\frac{5}{16}$ " round rods with rollers for a strong easy functioning latching system. No added holes or cutouts in enclosure are necessary for installation.



SCE-PLHG, pad lock latch.



SCE-MINIQL, pad lock latch.



SCE-DLCA, coin proof door latch.

All shown smaller than actual size.



SCE-KLWN, keylocking wing knob door latch.



SCE-PLWKB, padlocking wing knob.

All shown smaller than actual size.



SCE-DLSB, slotted door latch.



SCE-DLKLD, key-lock door latch.



SCE-DLWKC, wing knob latch.



SCE-ELKLH, "T" handle.



SCE-ELKL, Enviroline handle.



SCE-DL7SC, door latch with key.

To Order Visit omega.com/sce_acc for Pricing and Details

MODEL NO.	DESCRIPTION
SCE-3PTL	Enviroline® three-point latch kit

COIN PROOF DOOR LATCH		
SCE-DLCA	Chrome	¼ turn

PAD LOCK LATCHES		
SCE-PLHG	Black	¼ turn
SCE-MINIQPL	Stainless	Mini ¼ turn

MODEL NO.	FINISH	LATCH TYPE
SLOTTED 2 x 4 DOOR LATCH		
SCE-DLSB	Chrome	¼ turn
SCE-DLSBB	Black	¼ turn
SCE-DLSSB	Stainless	¼ turn
SCE-MINIQ	Chrome	Mini ¼ turn
SCE-MINIQB	Black	Mini ¼ turn

KEY-LOCK DOOR LATCH		
SCE-DLKLD	Chrome	¼ turn
SCE-DLKLDLDB	Black	¼ turn

PADLOCKING DOOR LATCH		
SCE-PLHG	Black	¼ turn
SCE-MINIQPL	Steel	Mini ¼ turn

WING KNOB DOOR LATCH		
SCE-DLWKC	Chrome	¼ turn
SCE-DLWKF	Black	¼ turn
SCE-MINIQLB	Black	Mini ¼ turn

KEY-LOCKING WING KNOB DOOR LATCH		
SCE-KLWN	Chrome	¼ turn
SCE-KLWNB	Black	¼ turn
SCE-MINIQLKB	Black	Mini ¼ turn

PADLOCKING WING KNOB DOOR LATCH		
SCE-PLWKB	Black	¼ turn

"T" HANDLE		
SCE-NLTH	Chrome	Non-locking - ¼ turn
SCE-ELKLH	Chrome	Locking - ¼ turn

HANDLE		
SCE-ELKL	Chrome	Key-locking handle - ¼ turn
SCE-ELPL	Chrome	Padlocking handle - ¼ turn

DOOR LATCH WITH KEY		
SCE-DL7TE	Chrome	7 mm triangular key - ¼ turn
SCE-DL5MDB	Chrome	5 mm double bit key - ¼ turn
SCE-DL5MDBB	Black	5 mm double bit key - ¼ turn
SCE-DL7SC	Chrome	7 mm square key - ¼ turn
SCE-DL8SC	Chrome	8 mm square key - ¼ turn
SCE-DL8SB	Black	8 mm square key - ¼ turn
SCE-MINIQ6MS	Black	6 mm square key - mini ¼ turn

Ordering Examples: SCE-3PTL, Enviroline three-point latch kit and SCE-ELPL, padlocking chrome handle to fit ¼ turn latch hole.

SCE-DLWKF, black wing knob door latch and SCE-KLWNB, key-locking black wing knob door latch to fit ¼ turn latch hole.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters