

NEW -- UNIVERSAL FEMALE! NEW -- STANDARD AND MINIATURE!

Universal Connector Write-On Female

Works with ALL *Miniature* and *Standard* Connectors
Type USTW Glass-Filled Nylon
Rated from -29 to 220°C (-20 to 425°F)



USTW-K-F
Patented Connector Fits
Both Standard and
Miniature Connectors


\$3.40

USTW Female



"FITS ALL"

- > 2 Connectors in 1
- > Universal Female Fits Both Miniature and Standard Connectors
- > Removable/Reversible Write-On Window
- > Accepts Stranded or Solid Wire Up to Size 14 AWG
- > Fully Compatible with OMEGA's as well as All Industry Miniature AND Standard-Size Thermocouple Connectors



USTW-K-F

All connectors shown approximately actual size.



2 Connectors in 1!
Fits Standard and Miniature Connectors

"FITS ALL"

PATENTED

Covered by U.S. and International patents and pending applications

Discount Schedule—See page G-18

To Order (Specify Model Number) IN STOCK FOR FAST DELIVERY!

Alloy Code [†]	Compensating Alloy Used in Connector		Shell Color	Write-on Window Style	Price Female (F)
	+	-			
K	CHROMEGA®	ALOMEGA®	Yellow	USTW-K-F	\$3.40
T	Copper	Constantan	Blue	USTW-T-F	3.40
J	Iron	Constantan	Black	USTW-J-F	3.40
E	CHROMEGA®	Constantan	Purple	USTW-E-F	3.40
R/S	Copper	Alloy #11	Green	USTW-R/S-F	3.40
U	Copper	Copper	White	USTW-U-F	3.40
N	OMEGA-P®	OMEGA-N®	Orange	USTW-N-F	5.10

[†] J, K, T, E, R, S and B are ANSI designations. OMEGA-P® and OMEGA-N® are generically known as nicrosil-nisil.

Note: Type U (uncompensated) connectors are used with Type B thermocouples (Pt/6%Rh-Pt/30%Rh).

Prices in U.S. Dollars

Ordering Example

Model USTW - K - F \$3.40

USTW - K - F

Universal Connector	Window Style	Calibration	Female (only)
---------------------	--------------	-------------	---------------



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters