




TYPE 4 ENVIROLINE[®] SERIES FREE-STANDING STEEL ENCLOSURES

Starts at
£520

- 0.104" Carbon Steel
- Seams Continuously Welded and Ground Smooth
- Oil-Resistant Gasket
- Flange Trough Collar Around All Sides of Door Opening
- Concealed Hinge
- Removable and Interchangeable Doors
- Black Quarter Turn Latches
- Removable Print Pocket
- Lifting Eyes for Easy Handling
- Ground Studs on Door and Body
- Mounting Channels Welded Horizontally on Sides of Interior Body at Top, Bottom and Middle for Mounting Optional Panels or Rack Mounting Angles
- No Door Stiffeners
- Padlocking or Keylocking Handle with 3-Point Operating Mechanism and Tamper-Resistant Hardware is Available
- Interchangeable Latches and Handles Available

SCE-72EL2418FS,
£520, shown smaller
than actual size.





Application


Designed to house electrical and electronic controls, instruments and components. Provides protection from dust, oil and water. For outdoor application a drip shield is recommended.

Finish


ANSI-61 gray coating inside and out over phosphatized surfaces. Optional panels are powder coated white.

Industry Standards

NEMA Type 4, 12, & 13
UL Listed Type 4 & 12
CSA Type 4 & 12
IEC 60529 IP 66



LATCH NOTE:
Omit center latch top and bottom of door when door width is ≤ 30.00 [762]



Dimensions: in (mm)

TYPE 4 ENVIROLINE SERIES FREE-STANDING ENCLOSURE

To Order (Specify Model Number)

IN STOCK FOR FAST DELIVERY!

TYPE 4 FREE STANDING STEEL ENCLOSURES

MODEL NO.	PRICE	HEIGHT (in) (A)	WIDTH (in) (B)	DEPTH (in) (C)
SCE-72EL2418FS	£520	72.00	24.00	18.00
SCE-72EL3024FS	635	72.00	30.00	24.00
SCE-72EL3624FS	690	72.00	36.00	24.00

Ordering Example: SCE-72EL2418FS Type 4 free standing carbon steel enclosure, £520.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters