

WATER LEAK ALARM



LA-13
\$18



- ✓ Battery Powered Sensors Can Be Placed Anywhere
- ✓ Stainless Steel Sensors
- ✓ Alarm >80 dB Loud That Runs for 3 Days
- ✓ Low-Battery Indication

The LA-13 portable water leak alarm can prevent potential water damage by keeping it anywhere water is a potential danger. Each sensor can be placed in an upright or flat position near the base of potential water leaks.

The LA-13 can be placed near plumbing, sinks, aquariums, sump pumps, refrigerators, dishwashers, toilets, water heaters, basements, washing machines and garages.

SPECIFICATIONS

Dimension: 79.4 x 66.7 x 22.2 mm (3 1/8 x 2 5/8 x 7/8")

Power Supply: 9V battery (included)

Weight: Approximately 136 g (0.3 lb) with battery included

Alarm: 110 dB

Alarm Time: 3 days

Sensors: Stainless steel



LA-13, \$18, shown larger than actual size.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
LA-13	\$18	Water leak alarm

Accessories

Model No.	Price	Description
MN1604	\$3	Extra 9V alkaline battery
FW-338	99	Reference Book: The Automation, Systems, and Instrumentation Dictionary 

Comes complete with operator's manual and 9V battery.

Ordering Example: LA-13, water leak alarm, \$18.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters