

SMART RETROFIT KIT FOR PX750 TRANSMITTERS

PX751-SMART KIT



Convert Your PX750
Analog Transmitter
into a
"Smart" Transmitter!

Starts at
\$525

- ✓ **The Most Economical Way to Convert a Loop to "Smart"**
- ✓ **Simple Plug-In Design**
- ✓ **Compatible with PX750 Transmitters from 5 inH₂O to 6000 psi**
- ✓ **Integral Span and Zero Pushbuttons**
- ✓ **Digital HART® Communications Using HART® Protocol Without Interrupting Output Signals**

SPECIFICATIONS

Power Supply: 12 to 45 Vdc
max load = 43.5 x (Supply volts -12)

Rangeability: 15:1

Output: 4 to 20 mA, user selectable linear or square root; digital signal superimposed on 4-20 mA signal available to HART® protocol devices

The PX750-SMART-KIT is the most economical way to obtain the benefits of "smart" electronics. The Smart electronics is a single board that is backward compatible with the installed base of PX750 transmitters with ranges from 5 inH₂O to 6000 psi. The retrofit kit allows remote communications, reranging and self diagnostics. A retrofitted transmitter features integral zero and span buttons for convenient reranging at the transmitter site. The electronics are also capable of linear and square root outputs which are software selectable. Failure alarm mode, adjustable damping, and transmitter security features are also standard.

The retrofitted PX750 communicates with the HART communicator and any other hosts implementing the HART communications protocol.

The PX750-SMART-KIT is easy to install, 5 easy steps convert your analog transmitter to a smart transmitter. The kit contains everything needed to convert a PX750 analog transmitter into a HART® ready "smart" transducer. Included is the smart electronics package, circuit board spaces, terminal eyelets, standoffs, cover and cover O-ring.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

TYPE	MODEL NO.	PRICE	COMPATIBLE MODELS
Differential or Gage Pressure	PX750-SMART-KIT	\$525	PX750-xxxGI, PX750-xxxDI PX750-xxxHDI, PX750-06DI

Kit includes all necessary parts plus complete operator's manual.

Ordering Example: To convert a PX750-30DI analog transmitter to a smart transmitter, order **PX750-SMART-KIT**, \$525.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters