


# “Banjo” Style Thermistor Sensor



ON-408-PP  
**\$156**



- ✓ 300 Series Stainless Steel, Hermitically Sealed Unit
- ✓ Extremely Sensitive Sensor with Thin Cross-Section Tip Combined and Ultra-Small Diameter Extension Sheath
- ✓ Measures Skin and Oral Temperatures, Water Baths, Air and Surface Temperatures

**AVAILABLE FOR FAST DELIVERY!**

| To Order (Specify Model Number) |       |                   |                                |               |              |                   |
|---------------------------------|-------|-------------------|--------------------------------|---------------|--------------|-------------------|
| Model No.                       | Price | Resistance @ 25°C | Interchangeability @ 0 to 70°C | Max Temp      | Cable Length | Cable Termination |
| ON-408-PP                       | \$156 | 2252 Ω            | ±0.1°C                         | 100°C (212°F) | 3 m (10')    | Phone plug        |

## Accessories

| Model No. | Price | Description   |
|-----------|-------|---|
| 450-ATH   | \$295 | Handheld thermometer, thermistor input  |
| 865F      | 199   | Thermistor meter; in 0.1°F resolution mode, -70.0 to 40.1°F, -40.0 to 199.9°F |
| DP25-TH-A | 325   | Thermistor input meter/controller with analog output                          |
| HH41      | 400   | Handheld thermistor thermometer   |

**Ordering Example:** ON-408-PP, “banjo” style thermistor sensor, 2252 Ω at 25°C, interchangeability of ±0.1°C, 3 m (10') of cable with a phone plug connector, \$156.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters