



STRAIN GAGE ACCESSORIES

APPLICATION KIT

SG1-KIT
£399

- ✓ Tools
- ✓ Adhesives
- ✓ Coatings
- ✓ Strain Gage Assortment



The SG1-KIT contains all the necessary tools to apply strain gages, plus an assortment of popular strain gages.

SG1-KIT, £399, shown smaller than actual size. Not all kit contents shown here.

KIT CONTENTS

- ✓ **Strain Gages (10/Pkg):**
 - SG-3/350-LY11 (Ribbon Leads)
 - SGD-7/350-LY41 (Solder Pads)
 - KFG-10-120-C1-11L1M2R (Lead Wire)
 - BTP-1 (Terminal Pads)
 - BTP-2 (Terminal Pads)
- ✓ **Coatings:** ABM75 Aluminum Foil with Putty
- ✓ **Adhesives:**
 - SG401 (0.1 oz)
 - SG496 (1 oz)
- ✓ **Application Note:** Guide to Applying Strain Gages/Manual

Tools:

- Flat Brush
- Fold-Out 6x Magnifier
- 12" Ruler
- 10' Flexible Ruler
- Glass Fiber Eraser
- Scissors, Dented
- Scissors, Pointed
- Dental Probe with Bent Point
- Dental Spatula for Cement
- Stripper for Removing Insulation
- Knife with 6 Blades
- 10' Roll of Multicolor Ribbon Cable
- Roll of Mylar® Tape
- Sheet of 180-, 240-, 400-Grade Emery Cloth
- Straight Tweezers
- Curved Tweezers
- Rugged Carrying Case

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
SG1-KIT	£399	Complete strain gage application kit

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ME-1805	£104	Reference Book: Instrumentation Fundamentals



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters