

483 mm (19") Universal Jack Panels

Accepts Standard and Miniature Connectors



ANSI color code shown
To order IEC color code visit omega.com


483 mm (19") Plain Jack Panels

No. of Rows	Panel Height	Max No. of Jacks
1	89 mm (3 1/2")	22
2	133 mm (5 1/4")	44
3	178 mm (7")	66
4	222 mm (8 3/4")	88

483 mm (19") Jack Panels with Switch Cutout

No. of Rows	Panel Height	Switch Size	Max No. of Jacks
1	133 mm (5 1/4")	76 mm (3")	15
2	133 mm (5 1/4")	76 mm (3")	30
2	178 mm (7")	127 mm (5")	30
3	178 mm (7")	127 mm (5")	45
4	222 mm (8 3/4")	127 mm (5")	60


Note: When a switch is ordered with a panel, installation is included at no extra charge, add suffix **"-MTG"** to model number of switch or meter. Panels with switches and/or meters are not supplied wired. Wiring charge is an additional cost per circuit. Consult factory for details.



PATENTED

Covered by U.S and International patents and pending applications

Consult Sales Department for information on custom, color-coded anodized panels.



OSW3
Visit omega.com/osw_sw14

DP460 Series
Visit omega.com/dp460-t

Shown smaller than actual size

To Order Visit omega.com/19ujp for Pricing and Details

Model No. ANSI Color Code	Total No. of Jacks	Switch Cutout	Meter Cutout
19UJP1-10-(*)	10	-	-
19UJP1-20-(*)	20	-	-
19UJP2-20-(*)	20	-	-
19UJP2-28-(*)	28	-	-
19UJP2-30-(*)	30	-	-
19UJP3-30-(*)	30	-	-
19UJP4-40-(*)	40	-	-
19UJP1-10-(*)-OSW	10	76 mm (3")	-
19UJP3-30-(*)-OSW	30	127 mm (5")	-
19UJP4-40-(*)-OSW	40	127 mm (5")	-
19UJP1-10-(*)-OSW-MTR	10	76 mm (3")	Yes
19UJP3-30-(*)-OSW-MTR	30	127 mm (5")	Yes
19UJP4-40-(*)-OSW-MTR	40	127 mm (5")	Yes

*Insert calibration code in model number: J, K, T, E, R, S or U.
Ordering Example: 19UJP1-10.

483 mm (19") Jack Panels with Switch and Meter Cutouts

No. of Rows	Panel Height (mm/inch)	Switch Size (mm/inch)	Max No. of Jacks
1	133 (5 1/4")	76 (3")	10
2	133 (5 1/4")	76 (3")	20
2	178 (7")	127 (5")	20
3	222 (8 3/4")	127 (5")	30
4	222 (8 3/4")	127 (5")	40

Note: A 1/2 DIN (45 x 92 mm) meter cutout is supplied unless otherwise specified.

Extra Supply of our Patented Design Dust Caps SPJ-CAP-12 pkg of 12

