

NEW

HAZARDOUS AREA HEATER 50 W, 100 W

CREX020 Series
Starts at
\$169

CREX02002010001, \$169,
shown smaller than
actual size.



- Large Convection Surface
- Clip Fixing
- Ready for Use
- Maintenance Free

Compact convection heater for use in areas with explosion hazard for prevention of formation of condensation, temperature fluctuations and for protection against frost in transmitter housings, switch cabinets and measuring equipment.

SPECIFICATIONS

Explosion Protection According to EN: LCIE (Laboratoire Central des Industries Electriques)

Conformity Certificate: 01 ATEX 6073/03, LCIE N° 06 ATEX Q8011, IECEx LCI 07.0020

Heating Element: High performance cartridge

Heater Body: Aluminium profile, black anodised

Connection: Si HF-JZ 3 x 0.75 mm² (0.03 in²) cable, length 1 m (3.3')

Connection PE: 4 mm² (0.16 in²)

Mounting Clip: 35 mm (1.4") DIN rail, EN 50022



Fitting Position: Vertical

Operating/Storage Temperature:

-20 to 40°C (-4 to 104°F)/-45 to 70°C (-49 to 158°F)

Protection Type/Protection Class:

NEMA 4 (IP65)/I (earthed)



MODEL NO.	CREX02010000	CREX02011001
Operating Voltage	110 to 120 Vac	110 to 120 Vac
Heating Capacity	50 W	100 W
Ex Protection Type	d IIC T5 - Ex tD A21 IP6X T100°C	d IIC T4 - Ex tD A21 IP6X T135°C
Surface Temperature	100°C (212°F)	135°C (275°F)
Length (L)	150 mm (6")	180 mm (7.1")
Weight (Approx.)	1.30 kg (46 oz)	1.50 kg (53 oz)



To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	DESCRIPTION
CREX02002010001	\$169	Enclosure heater, explosion-proof, 50 W, 120 Vac
CREX02002011001	206	Enclosure heater, explosion-proof, 100 W, 120 Vac

Comes complete with operator's manual.

Ordering Examples: CREX02002010001, hazardous area heater, \$169.
CREX02002011001, hazardous area heater, \$206.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters