


NEMA TYPE 1 SINGLE-DOOR ENCLOSURES



SCE-LP Series



SCE-10N804LP
shown smaller
than actual size.



- 0.060 and 0.075" Carbon Steel Depending on its Size
- Spot Weld Construction
- Standoffs Provided for Mounting Optional Panels
- Doors Open 180°
- Black Quarter Turn Latches
- Latches Are Opened or Closed with a Screwdriver
- Ground Stud On Door
- Mounting Holes in Back of Enclosure
- Subpanel Mounting Hardware

SCE-6N604LP shown
smaller than actual size.





Application


Designed to house electrical controls, instruments and components in areas that do not require oil, water and dust tight protection.

Finish

ANSI-61 gray powder coat inside and out over phosphatized surface. Optional panels are powder coated white.

Industry Standards

NEMA Type 1
UL Listed Type 1
CSA Type 1
IEC 60529 IP 30





To Order Visit omega.com/sce_lp for Pricing and Details

TYPE 1 SINGLE-DOOR ENCLOSURES

ENCLOSURES (inch)				SUB-PANEL (inch)		
MODEL NO.	HEIGHT (A)	WIDTH (B)	DEPTH (C)	MODEL NO.	HEIGHT (D)	WIDTH (E)
SCE-6N604LP	6.00	6.00	4.00	SCE-6N6MP	4.00	4.00
SCE-8N604LP	8.00	6.00	4.00	SCE-8N6MP	6.00	4.00
SCE-8N804LP	8.00	8.00	4.00	SCE-8N8MP	6.00	6.00
SCE-8N806LP	8.00	8.00	6.00	SCE-8N8MP	6.00	6.00
SCE-10N804LP	10.00	8.00	4.00	SCE-10N8MP	8.00	6.00
SCE-10N806LP	10.00	8.00	6.00	SCE-10N8MP	8.00	6.00
SCE-10N1004LP	10.00	10.00	4.00	SCE-10N10MP	8.00	8.00
SCE-10N1006LP	10.00	10.00	6.00	SCE-10N10MP	8.00	8.00
SCE-12N1004LP	12.00	10.00	4.00	SCE-12N10MP	10.00	8.00
SCE-12N1006LP	12.00	10.00	6.00	SCE-12N10MP	10.00	8.00
SCE-12N1204LP	12.00	12.00	4.00	SCE-12N12MP	10.00	10.00
SCE-12N1206LP	12.00	12.00	6.00	SCE-12N12MP	10.00	10.00
SCE-12N1208LP	12.00	12.00	8.00	SCE-12N12MP	10.00	10.00
SCE-14N1204LP	14.00	12.00	4.00	SCE-14N12MP	12.00	10.00
SCE-14N1206LP	14.00	12.00	6.00	SCE-14N12MP	12.00	10.00
SCE-14N1208LP	14.00	12.00	8.00	SCE-14N12MP	12.00	10.00
SCE-16N1206LP	16.00	12.00	6.00	SCE-16N12MP	14.00	10.00
SCE-16N1208LP	16.00	12.00	8.00	SCE-16N12MP	14.00	10.00
SCE-16N1606LP	16.00	16.00	6.00	SCE-16N16MP	14.00	14.00
SCE-16N1608LP	16.00	16.00	8.00	SCE-16N16MP	14.00	14.00
SCE-16N2006LP	16.00	20.00	6.00	SCE-20N16MP	18.00	14.00
SCE-20N1606LP	20.00	16.00	6.00	SCE-20N16MP	18.00	14.00
SCE-20N1608LP	20.00	16.00	8.00	SCE-20N16MP	18.00	14.00
SCE-20N2006LP	20.00	20.00	6.00	SCE-20N20MP	18.00	18.00
SCE-20N2008LP	20.00	20.00	8.00	SCE-20N20MP	18.00	18.00
SCE-20N2010LP	20.00	20.00	10.00	SCE-20N20MP	18.00	18.00
SCE-24N1606LP	24.00	16.00	6.00	SCE-24N16MP	22.00	14.00
SCE-24N2006LP	24.00	20.00	6.00	SCE-24N20MP	22.00	18.00
SCE-24N2008LP	24.00	20.00	8.00	SCE-24N20MP	22.00	18.00
SCE-24N2010LP	24.00	20.00	10.00	SCE-24N20MP	22.00	18.00
SCE-24N2406LP	24.00	24.00	6.00	SCE-24N24MP	22.00	22.00
SCE-24N2408LP	24.00	24.00	8.00	SCE-24N24MP	22.00	22.00
SCE-24N2412LP	24.00	24.00	12.00	SCE-24N24MP	22.00	22.00
SCE-30N2406LP	30.00	24.00	6.00	SCE-30N24MP	28.00	22.00
SCE-30N2408LP	30.00	24.00	8.00	SCE-30N24MP	28.00	22.00
SCE-30N2412LP	30.00	24.00	12.00	SCE-30N24MP	28.00	22.00
SCE-30N3008LP	30.00	30.00	8.00	SCE-30N30MP	28.00	28.00
SCE-36N2406LP	36.00	24.00	6.00	SCE-36N24MP	34.00	22.00
SCE-36N2408LP	36.00	24.00	8.00	SCE-36N24MP	34.00	22.00
SCE-36N2412LP	36.00	24.00	12.00	SCE-36N24MP	34.00	22.00
SCE-36N3006LP	36.00	30.00	6.00	SCE-36N30MP	34.00	28.00
SCE-36N3008LP	36.00	30.00	8.00	SCE-36N30MP	34.00	28.00
SCE-36N3012LP	36.00	30.00	12.00	SCE-36N30MP	34.00	28.00

Ordering Examples: SCE-6N604LP, Type 1 single-door enclosure.
SCE-16N2006LP, Type 1 single-door enclosure, SCE-20N16MP, sub-panel.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters