

Pressure, Humidity and Temperature Data Logger with LCD Display Part of the NOMAD® Family


OM-CP-PRHTEMP2000
Starts at
\$499



Optional

- ✓ Large Backlit LCD Display
- ✓ Front Keypad With Lock Feature
- ✓ User-Selectable Measurement Units
- ✓ Simultaneous Display of Temperature Humidity and Pressure
- ✓ NIST Traceable Calibration (Optional)
- ✓ Min/Max and Average Statistics
- ✓ Programmable Start/Stop Time
- ✓ Convenient Status Indicators
- ✓ User Replaceable Battery and External Power
- ✓ Wall Mountable

The OM-CP-PRHTEMP2000 is perfect for applications requiring instant remote readings of environmental parameters, including temperature, humidity and atmospheric pressure. The 8-button keypad and large LCD provide convenient access to current data and recorder setup. Additionally, memory and battery levels, external power status, sampling and recording status are shown on the LCD. Available on-screen data includes: statistics (min, max, average) for all three channels; recording status (start, stop and recording rate); display options (channels shown, units, text size); and calibration information (date calibrated, date for recalibration). Statistics can be cleared at any time during logging.



OM-CP-PRHTEMP2000, \$499, shown larger than actual size.

With 87,381 readings per channel, the OM-CP-PRHTEMP2000 has one of the largest memory capacities of any similar data recorder on the market. The non-volatile memory will retain recorded data, even if AC and battery power are lost.

The OM-CP-PRHTEMP2000 typically runs up to one month on a user-replaceable 9V battery (at a 1-minute reading rate with continuous LCD usage and no backlight). For further power savings, both the LCD and backlight have configurable auto-off options.

Those wanting to keep the LCD display and backlight continuously active need only to plug the unit to an optional AC power supply, keeping the 9V battery (included) connected as a back-up. NIST traceable calibration is available for users needing to meet regulatory requirements. Creating permanent records, performing data calculations, and the graphing of data is quick and easy: Simply connect the interface cable to an available USB or serial port and, with a few clicks of the mouse, data is downloaded and ready for review or export to Excel.

Specifications

TEMPERATURE

Range: -20 to 60°C (-4 to 140°F)

Resolution: 0.1°C

Calibrated Accuracy: ±0.5°C (0 to 50°C)

HUMIDITY

Range: 0 to 95% RH non-condensing

Resolution: 0.1% RH

Calibrated Accuracy: ±3% RH (±2% RH typical at 25°C)

Specified Accuracy Range: 10 to 40°C (50 to 104°F), 10 to 80% RH

PRESSURE

Range: 0 to 30 psia

Resolution: 0.002 psia

Calibrated Accuracy: ±1.0% FSR at 25°C; ±0.2% typical

DOT-MATRIX LCD

Dimensions:

35 H x 63 mm W (1.375 x 2.5")


Text: Configurable channel text size

Indicators: Power, status, memory

Backlight: Configurable w/auto shut-off and contrast adjustment

Start/Stop Time: Software programmable start time and date, up to six months in advance; programmable stop time

Memory: 87,381 readings per channel for a total of 262,143 total readings; software configurable memory wrap



OM-CP-IFC200, \$119, Windows software displays data in graphical or tabular format.

Reading Interval: 1 reading every 2 seconds to 1 every 24 hours

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Power: 9V lithium battery (included); optional AC adaptor

User Replaceable Battery: 30 days typical battery life

Data Format: Date and time stamped °C, °F, °K, °R; %RH, mg/ml water vapor concentration, dew point; psia, inHg, mmHg, bar, atm, Torr, Pa, kPa, MPa

Time Accuracy: ±1 minute/month at 20 to 30°C (68 to 86°F)

Computer Interface: PC serial or USB (interface cable required); 115,200 baud


Software: WIN98/NT/2000/XP/VISTA 32-bit (VISTA 32-bit version only; VISTA 64-bit is not supported)

Operating Environment: -20 to 60°C (-4 to 140°F), 0 to 95% RH non-condensing

Dimensions: 84 H x 122 W x 32 mm D (3.3 x 4.8 x 1.25")

Weight: 440 g (16 oz)

Enclosure: Black anodized aluminum



OM-CP-PRHTEMP2000, \$499, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-PRHTEMP2000	\$499	Pressure, humidity and temperature data logger with with LCD display
OM-CP-PRHTEMP2000-CERT	679	Pressure, humidity and temperature data logger with with LCD display and NIST calibration certificate
OM-CP-IFC110	99	Windows software and 1.2 m (4') RS232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	20	Replacement 9V lithium battery
OM-CP-110-PWR-2000	13	110 Vac power adaptor
OM-CP-220-PWR-2000	13	220 Vac power adaptor

Comes complete with operator's manual and 9V battery. The OM-CP-FC110, software, and RS232 cable (required to operate the data logger) are sold separately.

Ordering Example: OM-CP-PRHTEMP2000-CERT, pressure, humidity and temperature data logger with NIST calibration certificate, OM-CP-IFC110 Windows software, and RS232 cable, \$679 + 99 = \$778.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters