

24-Channel Open-Collector Output Board OME-DB-24C



\$209
Basic Unit

- ✓ 24 Open-Collector Outputs (NPN)
- ✓ One 50-Pin Connector, One 37-Pin D-Sub Connector and One 20-Pin Connector
- ✓ Maximum Load Voltage: 35 Vdc
- ✓ 3750 Vdc Optical Isolation
- ✓ LED Indicates Relay Status
- ✓ 8 High Current Outputs (600 mA)
- ✓ 16 Low Current Outputs (100 mA) Fuse Protected


The OME-DB-24C has 24 channels of optically isolated digital outputs, arranged into four isolated banks. Each digital output offers a darlington transistor and integral suppression diode for inductive load. The board interfaces to field logic signals, eliminating ground-loop problems and isolating the host computer from damaging voltages. The OME-DB-24C has one 37-pin D-sub connector, one 50-pin male and one 20-pin male connector.

The transistor is energized by applying a 5 V signal to the appropriate input channel on the

Compatible Data Acquisition Boards

Board	Cable	
	20 Pin*	50 Pin
OME-A-8111	✓	
OME-A-822PG	✓	
OME-A-826PG	✓	
OME-PCI-1002	✓	
OME-PCI-1202	✓	
OME-PCI-1602	✓	
OME-PCI-1800	✓	
OME-PCI-1802	✓	
OME-PCI-TMC12	✓	
OME-PIO-D144		✓
OME-PIO-D24	✓	
OME-PIO-D48		✓
OME-PIO-D56	✓	
OME-PIO-D96		✓
OME-PIO-DA4	✓	
OME-PIO-DA8	✓	

* Boards with 20-pin header provide support for only 16-channels



OME-DB-24C, \$209, shown smaller than actual size

50-pin connector, 20-pin flat cable connector or 37-pin D-sub connector. Twenty-four enunciator LED's, one for each transistor is activated.

Specifications

Voltage Load: 5-24 Vdc (external)
Channel 1-4 and 13-16: 600 mA per channel (max. load current)
Channel 6-12 and 17-24: 100 mA per channel (max. load current)

Power Consumption:

+5 V @ 0.4 A max, PC powered

Dimensions:

130 H x 220 mm W (5.1 x 8.7")

Operating Temperature:

0 to 60°C (32 to 140°F)

Storage Temperature:

-20 to 70°C (-4 to 158°F)

Humidity:

5 to 90% RH non-condensing

Max. Current Load Ext. Power (5-24 Vdc)	Low Nibble (4 Channels)	High Nibble (4 Channels)
Group A	600 mA	100 mA
Group B	100 mA	600 mA
Group C	100 mA	100 mA

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model Number	Price	Description
OME-DB-24C	\$209	24-channel open-collector output board, includes 1.5 m (5') 50-pin flat cable
OME-DB-24C/DIN	219	OME-DB-24C with DIN-rail mounting kit
OME-CA-2010	10	20-pin flat cable, 1 m (3')
OME-CA-2020	19	20-pin flat cable, 2 m (6.5')
OME-CA-3720	49	37-pin D-sub connector cable, 2 m (6.5')
OME-CA-5015	29	50-pin flat cable, 1.5 m (5')

Each board is supplied with complete operator's manual on CD ROM.

Ordering Example: OME-DB-24C 24-channel open-collector output board and OMEGACARESM 1 year extended warranty for OME-DB-24C (adds 1 year to standard 1 year warranty), \$209 + 25 = \$234.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters