

192-Channel Digital I/O Board

For IBM PC and Compatibles



Shown smaller than actual size



CIO-DIO192

Model CIO-DIO192

\$459

- 192 TTL Digital I/O Lines
- Each 50-Pin Connector Carries 48 Digital Lines Plus Power
- LabVIEW Drivers Available

The CIO-DIO192 can control 192 devices or sense 192 contact closures from a single card in a PC. The CIO-DIO192 employs eight 8255 parallel peripheral interface chips which are programmable in three modes; simple byte input or output or strobed I/O.

The CIO-DIO192 is a member of a family of digital I/O boards which use the 50-pin connector. Applications can easily be sized from 48 to 192 digital I/O points or more. Software is extensible to multiple points and all the accessories, including screw terminal boards, electro-mechanical relay boards and solid state relay boards interface to the same connector. Regardless of which digital I/O board is used.

Cabling and Connection

Cabling to the CIO-DIO192 is via standard 50-pin, 0.10" spacing AMP type ribbon cable connectors. Each cable carries 48 digital I/O lines, +5 V and ground. The CIO-DIO192 has four connectors.

The CIO-TERM100 screw terminal board provides 100 standard

12-22 AWG screw terminals. The CIO-MINI50 provides 50 such terminals. The SSS-RACK24 mounts 24 solid state relays, and the CIO-ERB24 mounts 24 electro-mechanical relays.

Each of the four connectors on the CIO-DIO192 carries 48 digital I/O lines. One 8255 circuit on pins 1-24 and one on pins 25-48.


Each 8255 has 24 I/O lines. The chip is configured as three ports. Two ports, A & B, are 8-bits wide, while port C may be an 8-bit port or two 4-bit ports.

Software

For those developing their own programs a software driver library is available. The Universal Driver Library provides software drivers compatible with most DOS and Windows 3.1/95/98/NT based languages. An optional LabVIEW driver is also available.



CIO-SCB-50



PCI-DIO192 Connector Diagram

To Order (Specify Model Number)

Model No.	Price	Description
CIO-DIO192	\$459	192 channel digital I/O board
CIO-TERM100	149	100 channel 16" x 4" screw terminal board; requires 2 C50FF-2 cables
CIO-MINI50	69	50 channel 4" x 4" screw terminal board; requires 1 C50FF-2 cable
CIO-SCB-50	199	50 conductor, shielded signal connection box
SSR-RACK24	149	24 channel solid state relay mounting rack
CIO-ERB24	249	24 channel electro-mechanical relay board; requires 1 C50FF-2 cable
C50FF-2	25	50-conductor connection cable, 2 ft
UNIV-DRVR	49	Universal Driver Library
CIO-LABVIEW-DRVR	49	LabVIEW Driver

Ordering Example: CIO-DIO192 digital I/O board with CIO-MINI50 terminal panels and OMEGACARESM 1-year extended warranty for CIO-DIO192 (adds 1 year to standard 3-year warranty), C50FF-2 cables, \$459 + 69 + 25 + 25 = \$578.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters