

BALL VALVES WITH LEVER HANDLE

BV80 Series
Starts at
\$29




- ✓ **Self Compensating Valve Stem Seal Design Ensures Long, Leak-Tight Maintenance Free Service**
- ✓ **Full Thread Length Compliance with ANSI B1.20.1 Specification Allows More Flexibility in L1 (hand) and L3 (wrench) Pipe Makeup for Handle Orientation and or Positive Sealing with Lesser Quality Mating Pipe Threads**
- ✓ **Machined Reinforced PTFE Seats and Stem Seal Standard for Uniform Operating Torque and Long Life**
- ✓ **Bar Stock Construction Offers Optimum Material Strength and Consistency**

The BV80 Series is a standard port, two-piece body offered in 1/4 thru 2" pipe size. Proper valve selection is dependent on your flow and functional requirements as well as physical size and value considerations.


The BV80 Series, all internal components, including the polymer seats, are precisely machined to strict tolerances, assuring repeated bubble tight sealing and maximum valve life. Our spring loaded stem seal provides automatic compensation for stem seal wear and thermal expansion and contraction. Each valve is bubble tested to ensure reliable, leak tight performance.

The BV80 Series are ideal for automation when coupled to our compact pneumatic or electric actuators.


The BVP80, BVPS80, and BVPE80 series are ball valves coupled to actuators.



BV81-SS, \$53, shown smaller than actual size.



Valve Size	Dimensions - inches					
	A	B	C	D	E	F
1/4 & 3/8	2.22	1.75	0.50	4.0	0.36	5.09
1/2	2.61	1.84	0.59	4.0	0.49	5.30
3/4	2.94	2.00	0.75	5.38	0.62	6.85
1	3.32	2.28	1.00	5.38	0.80	7.04
1 1/4	3.70	2.93	1.06	6.75	0.97	8.60
1 1/2	4.25	3.19	1.31	6.75	1.25	8.87
2	4.57	3.37	1.50	6.75	1.50	9.41



MOST POPULAR MODELS HIGHLIGHTED!

SPECIFICATIONS

Materials of construction
Body:

Brass: ASTM B-16
316SS: ASTM A276

Ball and Stem: 316 Stainless Steel

Seats and Stem Seal: Glass Reinforced PTFE

Temperature: -45 to 232°C (-50 to 450°F)

(see Pressure Temperature Chart)

Pressure: 49.6 bar (720 psi C.W.P.) [Cold Working Pressure to 65.5°C (150°F)] (see Pressure Temperature Chart)

Vacuum: 20 Micron

Saturated Stream: 10.3 bar (150 psi)

To Order (Specify Model No.)

Brass		316 Stainless Steel		FNPT Size
Model No.	Price	Model No.	Price	
BV81	\$29	BV81-SS	\$53	1/4"
BV82	29	BV82-SS	53	3/8"
BV83	39	BV83-SS	76	1/2"
BV84	45	BV84-SS	94	3/4"
BV85	65	BV85-SS	134	1"
BV86	83	BV86-SS	172	1 1/4"
BV87	106	BV87-SS	239	1 1/2"
BV88	155	BV88-SS	384	2"
CM-4449	75	Reference Book: Valve Selection Handbook		

Comes complete with operator's manual.

Ordering Examples: BV81, 1/4" FNPT ball valve, \$29. BV85-SS, 1" FNPT 316SS ball valve, \$134.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters