



Water-Resistant Conductivity/TDS Meters with Visual Alarm

CDH-721
\$75

- ✓ Automatic Temperature Compensation
- ✓ Selectable Setpoint and Red LED Alarm
- ✓ External 12 Vdc Power Supply
- ✓ Molded Hook for Quick Installation

The CDH-720 and TDS-720 Series water-resistant conductivity/TDS meters are OMEGA's reply to requests of accurate, low maintenance process monitoring equipment at affordable costs.

Four different models are available to cover all applications. Each meter is supplied with a direct 2 pin probe and 2 m (6.6') cable with a 1/2" thread for flow-thru mounting. The probe has a temperature sensor that will automatically compensate against temperature changes from 5 to 50°C (41 to 122°F) with a β of 2% per degree.

In the measurement mode, a red LED will warn the user in the event the reading is outside of the alarm interval. A front trimmer allows manual calibration at 1 point. The electrical circuitry is tightly sealed inside the water-resistant enclosure.

In addition, thanks to the molded hook, the CDH-720 and TDS-720 Series can be easily and quickly installed anywhere. The specially designed casing is stable and will not roll off a table. The 12 Vdc power supply makes it ideal for continuous monitoring over extended periods of time.

Specifications

Range:

CDH-721: 0 to 1990 μ S/cm
 TDS-721: 0 to 1990 ppm (mg/L)
 CDH-722: 0.00 to 9.99 mS/cm
 TDS-722: 0.00 to 9.99 ppt (g/L)

Resolution:

CDH-721: 10 μ S/cm
 TDS-721: 10 ppm
 CDH-722: 0.01 mS/cm
 TDS-722: 0.01 ppt

Accuracy (@68°F): \pm 2% full scale

Calibration: Manual single point through front trimmer

Setpoint:

CDH-721: 200 to 1600 μ S/cm
 TDS-721: 200 to 1600 ppm
 CDH-722: 0.70 to 3.50 mS/cm
 TDS-722: 0.70 to 3.50 ppt

Alarm:

CDH-721: 100 μ S/cm over setpoint
 TDS-721: outside setpoint by more than \pm 100 ppm
 CDH-722: outside setpoint by more than \pm 0.2 mS/cm
 TDS-722: outside setpoint by more than \pm 0.2 ppt

Probe:

CDH-721: CDE-721
 TDS-721: CDE-721
 CDH-722: CDE-722
 TDS-722: CDE-722

Power Supply: External 12 Vdc (included)

Environment:

0 to 50°C (32 to 122°F); RH 100%

Dimensions: 86 L x 94 W x 33 mm D (3.4 x 3.7 x 1.3")

Weight: 150 g (5.3 oz.)



CDE-722, \$30, replacement conductivity/TDS probe, shown larger than actual size.



CDH-721, \$75, conductivity meter with visual alarm, shown larger than actual size.

Comes complete with probe*, 12 Vdc adapter and operator's manual.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
CDH-721	\$75	Conductivity meter with visual alarm, 0 to 1990 μ S/cm
CDH-722	75	Conductivity meter with visual alarm, 0.00 to 9.99 mS/cm
TDS-721	75	TDS meter with visual alarm, 0 to 1990 ppm
TDS-722	75	TDS meter with visual alarm, 0.00 to 9.99 ppt
CDE-721	30	Replacement conductivity/TDS probe, 1/2" NPT, for CDH-721 and TDS-721
CDE-722	30	Replacement conductivity/TDS probe, 1/2" NPT, for CDH-722 and TDS-722
CDE-723	30	Replacement conductivity/TDS probe, 3/4" NPT, for CDH-721 and TDS-721
CDE-724	30	Replacement conductivity/TDS probe, 3/4" NPT, for CDH-722 and TDS-722
CDSA-450	10	450 microSiemen conductivity standard, 1 QT
CDSA-1500	10	1500 microSiemen conductivity standard, 1 QT
CDSA-4500	10	4500 microSiemen conductivity standard, 1 QT

*All probes come with 2 m (6.6') cable and 1/2" or 3/4" thread for flow-thru mounting.

Comes complete with probe, 12 Vdc adapter and complete operator's manual.

Ordering Examples: CDH-721, conductivity meter with visual alarm, \$75. TDS-722, total dissolved solids meter with alarm, \$75.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters