

OEM-STYLE ACRYLIC ROTAMETERS

**CAPACITIES: Water: 6.5 GPH to 20 GPM
Air: 2 SCFH to 62 SCFM**

FL7000 Series



Optional

- ✓ 50, 75, 100, 127, and 250 mm (1.97, 2.96, 3.94, 5, and 9.85") Scale Lengths
- ✓ Floats are Rod-Guided in Most Models
- ✓ Direct-Reading Scales

FL7000 OEM-style rotameters are precisely machined from solid acrylic blocks. They are available in 50, 75, 100, 127, and 250 mm scale lengths (1.97, 2.96, 5, 3.94, and 9.85") and have accuracies between 2 and 6%.

Model No.	Dimensions mm (inch)							Connection Size
	A	B	C	D	E	F	G	
FL7200	121 (4.8)	25 (1.0)	29 (1.1)	89 (3.5)	38 (1.5)	—	25 (1.0)	¼ FNPT
FL7300	165 (6.5)	35 (1.4)	35 (1.4)	127 (5.0)	64 (2.5)	8 (0.9)	32 (1.3)	½ FNPT
FL7400	213 (8.4)	44 (1.8)	46 (1.8)	197 (7.8)	133 (5.3)	32 (1.3)	32 (1.3)	1 FNPT
FL7500	235 (9.3)	35 (1.4)	35 (1.4)	168 (6.6)	102 (4.0)	8 (0.9)	33 (1.3)	½ FNPT
FL7600	346 (13.6)	44 (1.8)	46 (1.8)	302 (11.9)	203 (8.0)	32 (1.3)	64 (2.5)	¾ FNPT

To Order Visit omega.com/fl7000 for Pricing and Details

Water Model No.	Water Range*	Air Model No.	Air Range*	Pressure Drop (inH ₂ O)
FL7201	7.0 GPH	FL7211	2.6 SCFH	1.3
FL7202	12.0 GPH	FL7212	5.0 SCFH	2.2
FL7203	20.0 GPH	FL7213	10.0 SCFH	3.5
FL7204	50.0 GPH	FL7214	20.0 SCFH	7.0
FL7205	60.0 GPH	FL7215	30.0 SCFH	9.5
FL7206	75.0 GPH	FL7216	60.0 SCFH	11.8
—	—	FL7217	100.0 SCFH	—
—	—	FL7218	180.0 SCFH	—
—	—	FL7219	4.0 SCFM	—
FL7301	1.0 GPM	FL7311	4.0 SCFM	2.4
FL7302	2.0 GPM	FL7312	8.0 SCFM	4.6
FL7303	3.5 GPM	FL7313	14.5 SCFM	8.5
FL7304	5.0 GPM	FL7314	20.0 SCFM	12.2
FL7401	10.0 GPM	FL7411	40.0 SCFM	9.6
FL7402	15.0 GPM	FL7412	62.0 SCFM	17.3
FL7403	20.0 GPM	—	—	50.3
—	—	FL7511	4.0 SCFM	—
FL7503	2.0 GPM	FL7513	8.2 SCFM	4.8
FL7504	5.0 GPM	FL7514	20.0 SCFM	12.3
FL7601	2.0 GPM	FL7611	8.5 SCFM	2.7
FL7602	3.5 GPM	FL7612	14.5 SCFM	9.5
FL7603	5.0 GPM	FL7613	20.0 SCFM	31.4
FL7604	10.0 GPM	FL7614	40.0 SCFM	50.0

Comes complete with operator's manual.

* Minimum flow rate = 10% of maximum flow rate listed. ** For water units only.

For NIST calibration certificate add suffix "-NIST 5PT" for 5-point calibration, or suffix "-NIST 10PT" for 10-point calibration, for additional cost.

Ordering Examples: FL7302, acrylic rotameter for water, 2 GPM range.

FL7313, acrylic rotameter for air, 14.5 SCFM range.



FL7401 shown smaller than actual size.

FL7504 shown smaller than actual size.

SPECIFICATIONS

Construction: Acrylic tube, 316 SS float and guide rod (no guide rod for FL7211 through FL7215 air meters), PVC end fittings (brass on FL7200 series), EPR O-rings

Shipping Weights: FL7200, 7300, 7500: 0.45 kg (1 lb); FL7400: 0.79 kg (1.75 lb); FL7600: 1.25 kg (2.75 lb)

Maximum Pressure/Temperature:

Water Ranges:

125 psig at 21°C (70°F);

54°C (130°F) at 0 psig

Air Ranges: 100 psig at 21°C (70°F);


38°C (100°F) @ 0 psig

Full Scale Accuracy/Repeatability:

FL7200: 6/2%; FL7300: 6/1%;

FL7400: 4/1%; FL7500: 3/½%;

FL7600: 2/½%



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters