


SIGNAL CONDITIONERS FOR TURBINE METERS

Suitable for Direct Mounting onto FTB-900 and FTB9500 Series Flowmeters

All units are suitable for direct mounting onto the following turbines. (Refer to pages in this section) FTB-900 (page F-51), FTB-930 (page F-54), FTB9500 (page F-93), FTB-950 (pages F-53) and FTB-970A/980A (page F-55)



FLSC-64
\$271
As Shown

FLSC-61 \$431 0 to 5/0 to 10 Vdc Output

The FLSC-61 is a 3-wire analog transmitter designed to linearly convert a frequency input to an equivalent voltage output whose level is switch selectable @ 0 to 5V/0 to 10V. A full scale frequency range of 75 Hz to 10 kHz is jumper-selectable. The span adjustment establishes the frequency point at which the full scale voltage output (5 or 10V) is achieved. A sensitivity adjustment permits the FLSC-61 to discriminate between a signal input and noise.

SPECIFICATIONS

Temperature:

Operating: -40 to 85°C (-40 to 185°F)

Storage: -65 to 125°C (-85 to 257°F)

Input Voltage: 12 to 28 Vdc @ 50 mA max

Signal Input: Frequency 0 to 10 kHz; amplitude 50 mV to 35V sine or square-wave; impedance 10 kΩ

Analog Output: 0V @ 0 Hz, 5 or 10V @ desired full scale frequency

Full Scale Range: 75 Hz to 10 kHz, selectable

Response Time:

95% of change in 1 second

Linearity: 0.3% FS

Temperature Coefficient: <2% of rdg over entire temperature range

Minimum Load Resistance: 250 Ω

Enclosure: FM Approved; Class I, Groups, B, C, D; Class II, Groups E, F, G

Weight: 771 g (1.7 lb)

FLSC-62A \$431 4 to 20 mA Output

(Not Shown)

The FLSC-62A is a 2-wire loop-powered analog transmitter designed to linearly convert a frequency input to an equivalent 4 to 20 mA current output.

A full scale frequency range of 100 Hz to 10 kHz is switch selectable. The span adjustment establishes the frequency point at which a 20 mA output is achieved. A sensitivity adjustment permits the FLSC-62A to discriminate between signal input and noise.

SPECIFICATIONS

Input Voltage:

Minimum: 7V + (20 mA x RL)

Maximum: 28V + (4 mA x RL)

Analog Output: 4 mA @ 0 Hz, 20 mA @ desired full scale frequency

Full Scale Range: 100 Hz to 10 kHz, selectable

Response Time:

95% of change in 1 second

Linearity: 0.3% FS

Temperature Coefficient: <2% of rdg over entire temperature range

Minimum Load Resistance: 250 Ω

Maximum Load Resistance: 500 Ω

Enclosure: FM Approved; Class I, Groups, B, C, D; Class II, Groups E, F, G

Weight: 771 g (1.7 lb)

**ALL MODELS
AVAILABLE FOR
FAST DELIVERY!**

FLSC-64 \$271 Amplifier Squarewave Output

The FLSC-64 amplifies and conditions low-amplitude signals such as those developed by a magnetic pickup coil. The amplitude of the squarewave output equals the input supply voltage of the FLSC-64.

A sensitivity adjustment permits the FLSC-64 to discriminate between an input signal and noise. The

FLSC-64 contains a built-in test oscillator that enables the operator to verify the amplifier's operation without a signal source. The power LED illuminates when the input supply voltage is present.

SPECIFICATIONS

Temperature:

Operating: -40 to 85°C (-40 to 185°F)

Storage: -65 to 125°C (-85 to 257°F)

Input Voltage:

5 to 28 Vdc, 12 mA @ 12 Vdc

Signal Input:

Frequency: 0 to 10 kHz

Amplitude: 20 mV pp minimum

-35V sine or square-wave

Impedance: 10 kΩ

Output: 5 to 28 Vdc squarewave proportional to input voltage; minimum load @ 250 Ω; short circuit protection

Features: Individual LED indicators for power and output signal; built-in test oscillator that injects 4 Hz test signal when Test P/B depressed

Enclosure: FM Approved; Class I, Groups, B, C, D; Class II, Groups E, F, G

Weight: 771 g (1.7 lb)

Size: 142 W (without union coupling) x 61 D x 95 mm Dia. (5.6 x 2.4 x 3.75")



FLSC-61, \$431, shown mounted onto FTB-909 turbine, \$1335. See page F-51.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters