

# SINGLE AND DUAL SENSOR CONTROLLERS (AC)

LVCN-110/LVCN-20

**\$195**



- ✓ Mounts Directly on Sensor or OMEGA® Track System
- ✓ Rugged NEMA 4X (IP65) Enclosure
- ✓ Adjustable Time Delay
- ✓ Excellent for High or Low Level Alarm
- ✓ Controls Pumps, Valves and Alarms
- ✓ LED Displays Switch, Sensor and Relay Status

OMEGA's ac single sensor model LVCN-110 controller offers features normally found in much larger controllers. The adjustable time delay relay, invert switch, and LED status enunciators all maximize the flexibility of this powerful controller. High or low level alarm systems can easily be configured with this 120 to 240 Vac controller. The controller can be mounted on a sensor or OMEGA® track system, and is made of reinforced polypropylene. The controller swivels on its base for easy conduit alignment.

The LVCN-20 dual sensor controller is ideal for automatic filling or emptying operations. The controller conveniently mounts to a single sensor or to the sensor track system. This single channel controller offers a latching, automatic fill or empty operation between two sensor inputs. An adjustable time delay feature from 0 to 60 secs. before the relay responds assists in pump and valve protection. The invert and latch switch also expand the flexibility of the controller.



Shown smaller than actual size.

## SPECIFICATIONS

**Voltage Input:** Selectable, 120 or 240 Vac, 50 to 60 Hz.  
**Max Consumption:** 5 watts  
**Relay Output:** Isolated and sealed single pole double throw (SPDT) relay, Form C  
**Switching Mode:** Selectable, NO or NC states  
**Max Relay Switching Voltage:** 120 Vdc or 240 Vac  
**Max Switched Current:** 10 amps  
**Time Delay:** Adjustable from 0.15 to 60 seconds  
**Max Temp. Rating:** 70°C (158°F)  
**Sensor Voltage Supply:** Nominal 13.5 Vdc, 27 mA max.  
**Mounting Connection:** ¾ NPT  
**Conduit Connection:** ½ NPT  
**Enclosure Material:** (PP), flame retardant  
**Enclosure Rating:** NEMA 4X (IP65)  
**Dimensions:** 7.1 dia. x 11.9 cm H (2.8 x 4.7") x ¾ NPT

Level Track Mounting Systems May Be Used With the Following Sensors:

Item	Page
LVS-150	K-33
LVC-100	K-38
LVS-110	K-65

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description	Mat'l	Size
LVCN-110	\$195	Single sensor controller	PP	2.8 x 4.7 x ¾ NPT
LVCN-20	225	Dual sensor controller	PP	2.8 x 4.7 x ¾ NPT

## Accessory

Model No.	Price	Description
ES-2208	\$130	Reference Book: Hands On Water And Wastewater Equipment Maintenance Volume II 

Comes complete with operator's manual.

\* For CE approved, add suffix "-CE" to the model number and \$50 to price.

**Ordering Example:** LVCN-110, single sensor controller, \$195.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters