


# OMEGA-FLO® MINIATURE SOLENOID VALVES

SV-1200 Series Starts at

**\$106**



SV-1201, \$106, shown actual size.



- **Universal Functions:** 2/2-Way, Backpressure-Tight 3/2-Mixer or Distributor Valve
- **Low Dead Volume**
- **High Chemical Resistance**
- **Hermetic Isolation of Fluid Medium from Actuator**
- **Compact Design**
- **Monitoring Via LED**
- **Simple Electrical Connection**

SV-1200 Series miniature solenoid valves are ideal for applications in analysis technology, reliably handling difficult liquids such as acids, bases, pharmaceutical elements, and fluids in biotechnology processes. Thermal isolation of the actuator and fluid ensures accurate measurements for metering applications. A perfluorelastomer separation diaphragm hermetically isolates the fluid medium from the actuator. Other features include universal functions, small size, and simple and fast electrical connection to reduce installation costs. An LED provides safe and convenient monitoring.

## SPECIFICATIONS

### Valve

**Installation:** As required

**Seal Materials:**

Perfluorelastomer (Simriz®)

**Max Ambient Temp:** 60°C (140°F)

**Fluid Temperature Range:**

9 to 60°C (48 to 140°F)

**Orifice:** 1/16"

**Flow:** C<sub>v</sub> = 0.07

**Pressure Range:** 0 to 30 psi, vacuum; 10<sup>-3</sup> bar on request

**Response Time:** Approx. 30 ms

**Body Connections:** 1/8 NPT, 1/4-28 UNF-thread

### Actuator

**Operating Voltage:** 110 V, 50/60 Hz

**Voltage Tolerance:** ±10%

**Power Consumption:**


Approx. 3 W (hold)

**Cycling Rate:** Approx. 300 cpm

**Duty Cycle:** 100% continuous, 60% intermittent [with manifold assembly and simultaneous ambient and fluid temperatures >40°C (104°F)]

**Electrical Connection:** Cable plug

**Dimensions:** 68 H x 16 W x 32 mm D (2.7 x 0.6 x 1.3")



SV-1201, \$106, shown smaller than actual size.

(4) SV-1201, \$106 (each), shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)						
Model No.	Price	Connection	Body Material	Seal	Pressure Range (psi)	Back Pressure (psi)
<b>2-Way Valves (Normally Closed)</b>						
SV-1201	\$106	1/8 NPT	PVDF	Simriz	0 to 30	30
SV-1202	118	UNF 1/4-28"	ETFE	Simriz	0 to 30	15
<b>3-Way Valves (Normally Open or Closed Depending on Pressure Applied)</b>						
SV-1211	\$110	1/8 NPT	PVDF	Simriz	0 to 30	30
SV-1212	211	UNF 1/4-28"	ETFE	Simriz	0 to 30	15

Comes complete with operator's manual.

**Ordering Examples:** SV-1211, miniature 3-way solenoid valve, 1/8 NPT, PVDF material, 0 to 30 psi pressure and 30 psi back pressure ranges, \$110. SV-1201, miniature 2-way solenoid valve, 1/8 NPT, PVDF material, 0 to 30 psi pressure and 30 psi back pressure ranges, \$106.

### Accessory

Model No.	Price	Description
FW-350	\$49	Reference Book: Test Procedure for Control Valve Response Measurement from Step Inputs

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters