



Colorimeter Reagent Systems

- ✓ Over 50 Pre-Programmed Water Analysis Factors
- ✓ Automatic Wavelength Selection
- ✓ Friendly Menu-Driven Operation with Simple Six-Button Keypad

SC-1919
Starts at
\$825



The user-friendly SC-1919 Colorimeter is the direct reading colorimeter for complete on-site water analyses. All pre-programmed tests can be run on this compact instrument and each test features automatic wavelength selection. The entire multi-LED optical system is embedded in the light chamber and optimized for OMEGA test reagent systems. This enables the analyst to simply select the test and put in the sample with reagent. The microprocessor, which selects the wavelength, also allows the user to load up to 10 tests for analyzing custom reagent systems.

The SC-1919 Colorimeter is a portable, microprocessor controlled, direct reading colorimeter. It has a graphical 4 line, 16 character liquid crystal display for graphical, alphabetical and numerical messages. The operation is controlled with the keypad through menu driven software in response to selections shown on the display.

The test library consists of 100 tests (not all 100 may be available at present) and 10 "User Tests". The tests are precalibrated for the reagent systems. The colorimeter displays the results of these tests directly in units of concentration. The 10 "User Tests" may be used to enter additional calibrations. All of these tests may be arranged in any of 3 sequences. These sequences can be modified a limitless number of times to meet changing testing needs.

The optics feature 4 different colored LEDs. Each LED has a corresponding silicon photodiode with an integrated interference filter. The interference filters select a narrow band of light from the corresponding LED for the colorimetric measurements. The microprocessor automatically selects the correct LED/photodiode combination for a test. An RS-232 serial port on the back of the colorimeter, and optional software, allows the SC-1919 to be interfaced with a personal computer for real time data acquisition and data storage. This port also allows an interface with a RS-232 serial printer.

Due to its portability, alternate power sources, and rugged construction, the SC-1919 Colorimeter is ideal for lab and field use.



SC-1919, \$825 shown smaller than actual size.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
SC-1919	\$825	Colorimeter with 4 sample tubes, AC adapter, and instruction manual, 120 V/60 Hz
SC-1919-LCS	163	Large carrying case
SC-1919-SCS	97	Small field carrying case
SC-1912-CD-01	175	Interface cable/communication program on CD
ES-2253	99	Reference Book: Wastewater Treatment

Comes complete with 4 sample tubes, AC adaptor, battery, and instruction manual. For 230 V add **-230V**. No additional cost.

Ordering Example: SC-1919, digital colorimeter, SC-1912-CD-01 communication program and cable, SC-1919-SCS small carrying case, \$825 + 175 + 97 = **\$1097**.

Specifications

Light Source: LED/filter setup at 430nm, 520nm, 570nm, 630nm

Detector: Photodiode

Display: 122 x 32 LCD, 16 x 4 line graphics display

Range: 0 to 125%T

Resolution: 1% FS

Accuracy: 2% FS

CE Mark: Yes

Sample Cell: 25 mm (0.99") round cell, 10 mm (0.39") square cuvette, 16 mm (0.63") COD tubes

Order Online

Over 100,000 Products Available!



WATER & SOIL INSTRUMENTS

Power: 9 V battery or AC adapter (included)

Battery Life: 500 tests

Datalogging: RS-232, time and date stamped

Calibration: Factory set

Keypad: 6-button membrane switch

Size: 15 x 8 x 5.5 cm (6 x 3.25 x 2.5")

Weight: 900 g (2 lb)

The SC-1919 Colorimeter is complemented by easy-to-use reagent systems. Choose the desired test factors from the list below. Several packaging options are available for field use, making your SC-1919 Colorimeter a "field laboratory."

OMEGA uses ACS raw materials to manufacture reagent systems that have high reproducibility. We design our reagent systems to overcome test interference so results are fast and dependable.



SC-1919, \$825, shown smaller than actual size.

Model No.	Price	Test Factor	Range (ppm)	Test Method (# of Reagents)	# of Tests	Case Size*
SC-3641	\$61	Aluminum	0 to 0.3	Eriochrome Cyanine R (4)	50	L
SC-3659	40	Ammonia Nitrogen	0 to 1.0	Salicylate (3)	25	S
SC-3642	34	Ammonia Nitrogen	0 to 4.0	Nesslerization (2)	50	S
SC-3643-B	45	Bromine	0 to 9.0	DPD Tablets (2)	100	S
SC-3643-C	45	Chlorine	0 to 4.0	DPD Tablets (2)	100	S
SC-3644	27	Chlorine Dioxide	0 to 8.0	DPD Tablet/Glycine (2)	50	S
SC-3645	27	Chromium	0 to 1.0	Diphenylcarbazide (1)	100	L
SC-3646	14	Copper	0 to 6.0	Diethyldithiocarbamate (1)	100	S
SC-3640	23	Copper	0 to 3.5	Bicinchoninic Acid (1)	50	S
SC-3660	78	Cyanide	0 to 0.35	Pyridine-Barbituric Acid (5)	50	L
SC-3661	33	Cyanuric Acid	0 to 200	Melamine (1)	50	L
SC-3647	40	Fluoride	0 to 2.0	SPADNS (2)	50	L
SC-3656	48	Hydrazine	0 to 1.0	P-dimethylaminobenzaldehyde (2)	50	S
SC-3662	33	Hydrogen Peroxide	0 to 1.5	DPD Tablets (2)	100	S
SC-3648	33	Iron	0 to 6.0	Bipyridyl (2)	50	S
SC-3668	36	Iron	0 to 5.0	1,10 Phenanthroline (2)	50	S
SC-4031	63	Lead	0 to 5.0	PAR (5)	50	S
SC-3658	50	Manganese	0 to 0.5	PAN (3)	50	L
SC-3669	68	Manganese (HR)	0 to 15.0	Periodate (2)	50	S
SC-3699-01	45	Molybdenum	0 to 50	Thioglycolate (3)	50	L
SC-3663	87	Nickel	0 to 8.0	Dimethylglyoxime (6)	50	L
SC-3649	37	Nitrate	0 to 3.0	Cadmium Reduction (2)	20	S
SC-3650	37	Nitrite	0 to 0.8	Diazotization/Coupling (2)	20	S
SC-3688	36	Oxygen, Dissolved	0 to 11.0	Winkler Colorimetric (3)	200	S
SC-3651	185	Ozone	0 to 0.4	Indigo Trisulfonate (3)	100	L
SC-3700	40	pH	5.0 to 9.6	Colorimetric (3)	100	L
SC-3652	44	Phenols	0 to 6.0	4-Aminoantipyrine (3)	50	L
SC-3655	18	Phosphate (HR)	0 to 70.0	Molybdovanadate (1)	50	S
SC-3653	32	Phosphate (LR)	0 to 3.0	Ascorbic Acid Reduction (2)	50	S
SC-3639	47	Potassium	0.5 to 10.0	Tetraphenylboron (2)	100	S
SC-3664	44	Silica	0 to 4.0	Heteropoly Blue (4)	100	S
SC-3687	33	Silica (HR)	0 to 75	Silicomolybdate	50	S
SC-3665	23	Sulfate	0 to 100	Barium Chloride (1)	100	S
SC-3654	52	Sulfide	0 to 3.0	Methylene Blue (3)	50	L
SC-3666	41	Tannin	0 to 10	Tungsto-Molybdophosphoric Acid (2)	50	L
SC-3667	89	Zinc	0 to 3	Zincon (6)	50	L

Kit contents vary. Each kit comes complete with everything necessary to perform the specified test.

Ordering Example: SC-3641, aluminum reagent test kit, \$61.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters