

FLANGED IMMERSION HEATERS FOR MILD CORROSIVE SOLUTIONS



TMS Series

- ✓ 240 and 480 V, 1 & 3 Phase
- ✓ 3 to 36 kW
- ✓ Premium Grade Stainless Steel (8% Nickel) Sheathed Heating Elements for Use in Mild Corrosive Solutions
- ✓ Time Tested
- ✓ Heavy Duty

FEATURES

Rugged construction. Sturdy stainless steel .475" (1.2 cm) diameter elements, welded to steel flanges provide superior rigidity and strength. Heavy duty jumper straps and terminal parts assure permanent tightness of connections and an extra margin of current carrying capacity.

Long life elements. High grade 304 series stainless steel outer sheath provides the benefits of strength and durability in those applications where stainless performance is required.


SPECIFICATIONS

Wattage: 3 to 36 kW
Power: 240 and 480 V, 1 & 3 phase
Watt Density: 23 W/in²
Terminal Enclosure: General purpose NEMA 1 rated. Other enclosures available. Contact OMEGALUX®

Please Note: Approved pressure and/or temperature limiting controls must be used to assure safe operation in the event of system malfunctions. See Temperature Section. Heaters with General Purpose & Moisture Resistant Enclosures are UL Listed and CSA Certified and Not Intended for use in Hazardous Areas.

Ordering Example: Model
 TMS-3035M/240/3P Is a 3 kW heater powered by 3 phase 240 VAC, **\$837.**

Ordering Example: Model
 TMS-6095M/480/3P Is a 9 kW heater powered by 3 phase 480 VAC, **\$1526.**



To Order (Specify Model Number)

kW	Circ.	Dim. in. (cm) B	E-1 General Purpose Encl. ¹		Wt. lb (kg)	Dim. in. (cm) N
			Model No.	Price		
3 Inch-150 lb. Steel Flange, 3 Stainless Steel Elements — 23 W/in²						
3	1	18 ¹ / ₆ (46)	TMS-3035M/240/*	\$837	16 (7)	1 (3)
3	1	18 ¹ / ₆ (46)	TMS-3035M/480/*	837	16 (7)	1 (3)
4.5	1	25 ³ / ₆ (64)	TMS-3045M/240/*	961	17 (8)	1 (3)
4.5	1	25 ³ / ₆ (64)	TMS-3045M/480/*	961	17 (8)	1 (3)
6	1	33 ³ / ₆ (84)	TMS-3065M/240/*	1125	18 (8)	1 (3)
6	1	33 ³ / ₆ (84)	TMS-3065M/480/*	1125	18 (8)	1 (3)
7.5	1	40 ³ / ₆ (103)	TMS-3075M/240/3P	1266	19 (9)	1 (3)
7.5	1	40 ³ / ₆ (103)	TMS-3075M/480/3P	1266	19 (9)	1 (3)
9	1	48 ³ / ₆ (122)	TMS-3095M/480/*	1435	21 (10)	1 (3)
9	1	48 ³ / ₆ (122)	TMS-3095M/240/3P	1435	21 (10)	1 (3)
5 Inch-150 lb. Steel Flange, 6 Stainless Steel Elements — 23 W/in²						
9	1	25 ³ / ₆ (64)	TMS-6095M/**/3P	1526	32 (15)	1 (3)
12	1	33 ³ / ₆ (84)	TMS-6125M/**/3P	1690	33 (15)	1 (3)
15	1	40 ³ / ₆ (103)	TMS-6155M/**/3P	1949	35 (16)	1 (3)
20	2	52 ¹ / ₆ (46)	TMS-6205M/240/3P	2388	38 (17)	1 (3)
20	1	52 ¹ / ₆ (46)	TMS-6205M/480/3P	2388	38 (17)	1 (3)
25	2	65 ¹ / ₆ (64)	TMS-6255M/240/3P	2779	42 (19)	1 (3)
25	1	65 ¹ / ₆ (84)	TMS-6255M/480/3P	2779	42 (19)	1 (3)
30	2	78 ³ / ₆ (84)	TMS-6305M/**/3P	3277	46 (21)	1 (3)
6 Inch-150 lb. Steel Flange, 12 Stainless Steel Elements — 23 W/in²						
18	2	25 ³ / ₆ (64)	TMS-1218M/**/3P	3174	67 (30)	1 (3)
24	2	33 (84)	TMS-1224M/**/3P	3372	76 (34)	1 (3)
30	2	40 ¹ / ₂ (103)	TMS-1230M/**/3P	3510	84 (38)	1 (3)
36	2	48 (122)	TMS-1236M/**/3P	3814	111 (50)	1 (3)

/* Add the suffix "3P" to the model number for 3 phase power.
 /** Designate voltage, i.e., 240 for 240 VAC or 480 for 480 VAC.
 Note: Larger flange sizes and kW rating available. Contact OMEGALUX®



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters