

## HIGH WATT DRUM HEATERS AND INSULATING BLANKETS

DRUM-DHW-55 Series

**\$270**

All Models



- ✓ Fits Standard 55 Gallon Metal Drums
- ✓ Built in Thermostat 10 to 218°C (50 to 425°F)
- ✓ 115 or 230 Vac Standard
- ✓ Simple Spring and Hook Arrangement
- ✓ Resistant to Mechanical Damage
- ✓ Chemical Resistant
- ✓ Freeze Protection or Temperature Maintenance Applications
- ✓ Built-In Metal Screen is Grounded Electrically for Safety
- ✓ UL Recognized Components

Omegalux® drum heaters can easily be wrapped around a drum and attached with a simple spring and hook arrangement. Once in position, the drum heater provides uniform and even heat to the contents of the drum. Omegalux® drum heaters are manufactured using a nickel alloy resistance wire and fully vulcanized fiberglass reinforced silicone rubber. They are resistant to mechanical damage and to attack from many chemical substances. The use of reinforced silicone rubber material as a base for the drum heater allows the design of extra flexible, very thin and efficient heaters. Each heater band is equipped with a 1.8 m (6') cord set (230 Vac heaters do not have a plug). A built-in metal screen is grounded electrically for safety. All heaters are high potential dielectric tested at 1500V at the factory. Drum heaters are available with either a 115 or 230V rating. When used with lightweight insulating blankets, drum heaters provide more efficient, more uniform heating with better temperature control. Designed for use with 55 gallon steel drums, the rugged



DRUM-DHW-55-115-TS, \$270, shown smaller than actual size.

TOTE-BH-55 Series

**\$920**

All Models

TOTE-BH-55-115-TS, \$920, shown smaller than actual size.



aluminized cloth has 25.4 mm (1") of fiberglass insulation- for less heat loss and increased worker safety. Provides outstanding freeze protection, as well as temperature and viscosity control. Velcro fasteners make installation easy for a single person.

### Specifications

**Power:** 115 and 230 Vac  
**Wattage:** 1000 or 1500 W  
**Max Ambient Operating Temp:** 148°C (300°F)  
**Max Exposure Temp:** 232°C (450°F)  
**Width:** 1.2 mm (4")  
**Power Cord:** 1.8 m (6') (230 Vac does not include plug)

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)			
Model No.	Price	Description	Watts
DRUM-DHW-55-115-TS	\$270	Flexible drum heater (115V)	1500
DRUM-DHW-55-230-TS	270	Flexible drum heater (230V)	1500
TOTE-BH-55-115-TS	920	Insulating blanket with heater (115V)	1000
TOTE-BH-55-230-TS	920	Insulating blanket with heater (230V)	1000
COVER-IB-55	760	Insulating blanket	—
PE-1018	220	Reference Book: The Control Handbook	

Ordering Example: DRUM-DHW-55-115-TS, 115V flexible drum heater for 55 gallon drum, \$270.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters