

FTH SERIES HEATERS





FTH Series
Starts at

\$525



FTH-6000-240,
\$550, shown
smaller than
actual size.

OMEGA® flow through heaters are designed primarily for providing heat that regulates liquid temperature from 32 to 88°C (90 to 190°F). The heaters have a titanium element that resists corrosion. The flow through tube is 381 mm (15") long and has 1 NPT female pipe connections and is available in 304 SS. The safety high limit trip point for the heater is 99°C (210°F). The 201 x 145 x 89 mm (7.9 x 5.7 x 3.5") enclosure is made of ABS plastic and is water resistant.





CAUTION AND WARNING!

- Not for use as a spa or hot tub heater
- Read all instructions before installation and operation
- Heater will fail if energized without proper fluid flow—15 GPM min
- Pump must be running and fluid flowing before turning on power to the heater
- Heater must be powered down for one to five minutes before turning off the pump and stopping fluid flow
- Bleed the system of any air before applying power to the heater
- Heaters failures due to insufficient flow or due to dry firing, the heater is not covered under warranty
- Heater should always be mounted so that the water outlet is elevated a minimum of 3" above the water inlet (see figure A)
- When using piping smaller than 1½", the heater is to be mounted in a vertical orientation. Fluid flow is to enter at the bottom and exit out the top (see figure B)
- Minimum connecting pipe diameter is ¾"
- Piping connections are to meet all local plumbing codes
- Electrical connections must be performed in accordance with articles 250 and 680 of the National Electric Code and by a qualified electrician

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	Price	Wattage	Voltage	Phase	AMP Draw
FTH-1500-120	\$525	1500	120	1 Ø	12.5
FTH-2000-240	525	2000	240	1 Ø	8.3
FTH-3000-240	525	3000	240	1 Ø	12.5
FTH-4000-240	525	4000	240	1 Ø	16.7
FTH-5000-240	550	5000	240	1 Ø	20.8
FTH-6000-240	550	6000	240	1 Ø	25.0

Comes complete with operator's manual.
Ordering Examples: FTH-1500-120, flow through heater, 1.5 kW, \$525.
 FTH-2000-240, flow through heater, 2 kW, \$525.



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters