



# SILICON/BRASS PRESSURE TRANSDUCERS WITH MILLIVOLT OUTPUT

**PX180B Series**  
0 to -14.7 to 0-500 psi  
0 to -1.0 to 0-34.5 bar

Starts at  
**\$165**



- ✓ Excellent Total Accuracy and Interchangeability
- ✓ Gage Pressure, Vacuum, and Compound Ranges Available
- ✓ Rugged, Compact Design
- ✓ RFI/EMI Protection
- ✓ Reverse Polarity Protection

OMEGA's PX180B Series transducers, designed for general industrial and commercial requirements, offer excellent performance in a wide range of applications. They are based on proven micro-machined silicon technology, providing high reliability, long-term stability, and low cost. They are extremely accurate, with less than 0.3% reference accuracy.

## SPECIFICATIONS

**Excitation:** 10 Vdc (regulated)

**Output:** 0 to 50 mV for 0 to 1 psi model, 0 to 100 mVdc for all other ranges

**Load Resistance:** 50,000 Ω minimum

**Accuracy:** 0.3% BFSI maximum (includes linearity, hysteresis and repeatability)

**Operating Temperature:**  
-40 to 80°C (-40 to 176°F)

**Compensated Temperature:**  
-25 to 75°C (-13 to 167°F)


**Process Temperature:**  
-40 to 100°C (-40 to 212°F)

**Thermal Zero Effect:** 2% FS maximum over compensated temperature range

**Thermal Span Effect:** 2% FS maximum over compensated temperature range

**1-Year Stability:** <0.25% FS

**Proof Pressure:** 2x FS (750 psig for 500 psig range)



PX180B-015GV, \$165, shown larger than actual size.



**WIRING:**  
Red = Ex +  
Black = Ex -  
Green = Sig +  
White = Sig -

**Burst Pressure:** 3x FS or 750 psig, whichever is less

**Wetted Parts:** Brass, borosilicate, silicon, RTV and epoxy

**Vibration:** 10 g, 55 to 2000 Hz

**Shock:** 30 g

**Process Connection:** 1/8 NPT male

**Electrical Connection:** 0.4 m (18") 24-gage shielded cable

**Weight:** 142 g (5 oz)

**Dimensions:** 1 1/2 hex; 72 H x 29.7 mm Dia. (2.84 x 1.17")

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)				
GAGE PRESSURE RANGES				
psi	bar	MODEL NO.	PRICE	COMPATIBLE METERS*
0 to -14.7	0 to -1.0	PX180B-015VACV	\$165	DP25B-S, DP41-S, DPiS Series
0 to 1	0 to 68.9 mbar	PX180B-001GV	185	DP25B-S, DP41-S, DPiS Series
0 to 6	0 to 414 mbar	PX180B-006GV	165	DP25B-S, DP41-S, DPiS Series
0 to 15	0 to 1.0	PX180B-015GV	165	DP25B-S, DP41-S, DPiS Series
0 to 30	0 to 2.1	PX180B-030GV	165	DP25B-S, DP41-S, DPiS Series
0 to 60	0 to 4.1	PX180B-060GV	165	DP25B-S, DP41-S, DPiS Series
0 to 100	0 to 6.9	PX180B-100GV	165	DP25B-S, DP41-S, DPiS Series
0 to 200	0 to 13.8	PX180B-200GV	165	DP25B-S, DP41-S, DPiS Series
0 to 300	0 to 20.7	PX180B-300GV	165	DP25B-S, DP41-S, DPiS Series
0 to 500	0 to 34.5	PX180B-500GV	165	DP25B-S, DP41-S, DPiS Series
-14.7 to 15	-1.0 to 1.0	PX180B-015CV	165	DP25B-S, DP41-S, DPiS Series
-14.7 to 30	-1.0 to 2.1	PX180B-030CV	165	DP25B-S, DP41-S, DPiS Series
-14.7 to 60	-1.0 to 4.1	PX180B-060CV	165	DP25B-S, DP41-S, DPiS Series

## ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
PS-8E	\$10	Pressure snubber for water or light oils
PS-8D	10	Pressure snubber for dense liquids or oils
PS-8G	10	Pressure snubber for gases and steam
GE-0624	110	Reference Book: The Wiley Engineer's Desk Reference

Comes with complete operator's manual.

\* See section D for compatible meters.

**Ordering Example:** PX180B-100GV, 0 to 100 psig transducer with 0 to 100 millivolt output, \$165.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters