

HEATING TAPES WITH BUILT-IN ADJUSTABLE THERMOSTAT

HTWAT Series
Starts at

£90



- ✓ Adjustable Thermostat Control Sets Up to 218°C (425°F)
- ✓ No Additional Control Needed
- ✓ Moisture and Chemical Resistant
- ✓ Suitable for Electrically Conductive Surfaces
- ✓ Rapid Heat Up



HTWAT051-002, £90, shown smaller than actual size.

 MOST POPULAR MODELS HIGHLIGHTED!

HTWAT Series silicone rubber heating tapes with adjustable thermostat control are designed for process temperature control, freeze protection, and supplemental heat. Applications include valves, pipe lines, bearings, filter housings, actuators and more. Wrap the flexible heating tape around the desired object you want to heat, set the temperature, and it will maintain heat at the set temperature.

SPECIFICATIONS

Adjustable thermostat:
10 to 218°C (50 to 425°F)

Maximum Exposure Temperature:
232°C (450°F)

Nominal Watt Density:
6.0 Watts/in V (0.009 Watts/mm V)

Minimum Bend Radius:
6.35 mm (0.25")

Outer Sheath:
Extruded silicone rubber

Construction:
Fiberglass, knitted and braided

Power Cord: 1.8 m (6') with plug on 120V models, stripped lead ends on 240V models

Power: 120 or 240 Vac

To Order (Specify Model Number)

120 Vac Power Model No.	240 Vac Power Model No.	Price	Power	Size mm x m (in x ft)
HTWAT051-002	HTWAT052-002	£90	72 W	12.7 x 0.6 (½ x 2)
HTWAT051-004	HTWAT052-004	96	144 W	12.7 x 1.2 (½ x 4)
HTWAT051-006	HTWAT052-006	100	216 W	12.7 x 1.8 (½ x 6)
HTWAT051-008	HTWAT052-008	106	288 W	12.7 x 2.4 (½ x 8)
HTWAT051-010	HTWAT052-010	115	360 W	12.7 x 3.0 (½ x 10)
HTWAT101-002	HTWAT102-002	287	144 W	25.4 x 0.6 (1 x 2)
HTWAT101-004	HTWAT102-004	283	288 W	25.4 x 1.2 (1 x 4)
HTWAT101-006	HTWAT102-006	226	432 W	25.4 x 1.8 (1 x 6)
HTWAT101-008	HTWAT102-008	316	576 W	25.4 x 2.4 (1 x 8)
HTWAT101-010	HTWAT102-010	500	720 W	25.4 x 3.0 (1 x 10)
HTWAT201-002	HTWAT202-002	131	288 W	50.8 x 0.6 (2 x 2)
HTWAT201-004	HTWAT202-004	141	576 W	50.8 x 1.2 (2 x 4)
HTWAT201-006	HTWAT202-006	147	864 W	50.8 x 1.8 (2 x 6)
HTWAT201-008	HTWAT202-008	153	1152 W	50.8 x 2.4 (2 x 8)
HTWAT201-010	HTWAT202-010	163	1440 W	50.8 x 3.0 (2 x 10)
HTWAT301-002	HTWAT302-002	146	432 W	76.2 x 0.6 (3 x 2)
HTWAT301-004	HTWAT302-004	156	864 W	76.2 x 1.2 (3 x 4)
HTWAT301-006	HTWAT302-006	163	1296 W	76.2 x 1.8 (3 x 6)
HTWAT301-008	HTWAT302-008	170	1440 W	76.2 x 2.4 (3 x 8)
HTWAT301-010	HTWAT302-010	180	1440 W*	76.2 x 3.0 (3 x 10)

* 240V version is 1800 W.

Comes complete with user's manual. 240V versions are supplied without plugs.

Ordering Examples: HTWAT201-002, heating tape, 2" x 2', 120V, 288 W, with integral adjustable thermostat, £131.

HTWAT051-002, heating tape, ½" x 2', 120V, 72 W with integral adjustable thermostat, £90.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters