

SUBMERSIBLE PRESSURE TRANSDUCER

FOR LEVEL AND DEPTH MEASUREMENT

38 mm (1.5") DIA.

Supplied with a desiccant.

PX78 Series
mV/V Output
0-4 to 0-15 psi
0-9.2 to 0-34.6' of water

Starts at
\$560




- ✓ All Stainless Steel Construction
- ✓ Hermetically Sealed Housing
- ✓ Screw-On Protective Cap Included
- ✓ 15 m (50') Vented Cable Standard
- ✓ Works with Optional In-Line Amplifiers

OMEGA's PX78 pressure transducer is fully submersible, designed for liquid level and depth measurement. Its all stainless steel hermetically sealed housing makes it suitable for immersion in most industrial liquids and oils. A standard 15 m (50') vented cable (longer lengths available) provides an atmospheric pressure reference. With a 5000 Ω bridge, the PX78 is designed to work with the DMD-16 and DMD-17 in-line amplifiers for long-distance transmission of the signal.

SPECIFICATIONS

Excitation: 10 Vac/Vdc (15 V max)
Output: 3 mV/V nominal
 2.5 mV/V ≤ 5 psig
Zero Balance: ±2% FSO
Input Resistance: 5000 Ω min
Output resistance: 5000 ±50 Ω
Accuracy: 0.5% FS includes linearity, hysteresis and repeatability combined
Operating Temp Range:
 -29 to 93°C (-20 to 200°F)



Compensated Temp Range:

16 to 71°C (60 to 160°F)

Span Error: 0.003% rdg/°F

Zero Error: 0.005% FSO/°F

Proof Pressure:

150% of rated pressure

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

psig	bar	ftH ₂ O	MODEL NO.	PRICE	COMPATIBLE METERS*
0 to 4	0 to 0.27	9.2	PX78U7-004GV	\$560	DP41-S, DP25B-S
0 to 5	0 to 0.34	11.5	PX78U7-005GV	560	DP41-S, DP25B-S
0 to 10	0 to 0.69	23.1	PX78U7-010GV	560	DP41-S, DP25B-S
0 to 15	0 to 1.0	34.6	PX78U7-015GV	560	DP41-S, DP25B-S

Comes with complete operator's manual.

Metric ranges available – consult Engineering.

* See section D for compatible meters.

To order with extra cable, add suffix “-(Length in feet) FT” and add \$3.50/ft beyond standard 15 m (50') length.


Ordering Examples: PX78U0-015GV-100FT, 15 psi transducer with 30 m (100') cable, \$560 + (50 x 3.50) = \$735. PX78U0-005GV, 5 psi transducer with the standard 15 m (50') cable, \$560.

ACCESSORIES (In-Line Amplifiers)

MODEL NO.	PRICE	DESCRIPTION
DMD-16V	\$165	0 to 5 V output, NEMA 4 (IP65) stainless steel case
DMD-17V	165	0 to 5 V output, NEMA 12 (IP54) enclosure
DMD-16I	165	4 to 20 mA output, NEMA 4 (IP65) stainless steel case
DMD-17V	165	4 to 20 mA output, NEMA 12 (IP54) enclosure

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
A019385	\$35	Replacement desiccant
ME-1756	110	Reference Book: Practical Injection Molding



PX78U7-005GV, \$560, shown smaller than actual size.

Burst Pressure:

300% of rated pressure

Wetted Parts:

316 stainless steel diaphragm and 17-4 PH stainless steel housing

Pressure Port: Nose protector included

Electrical Connection: 15 m (50') shielded and vented PVC cable

Notice: OMEGA does not offer a warranty on this product, its use, or application. It is the end user's responsibility to assure proper installation and use of this transducer.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters