

1/8 DIN Digital Proportional, On/Off Temperature Controller

CN1000 Series
\$395
 All Models

MONOGRAM
 SERIES

Panel punches available, visit omega.com/panelpunches

CN1001TC, \$395, shown smaller than actual size.



- ✓ Thermocouple and RTD Input Models
- ✓ Dual Programmable Setpoints
- ✓ Analog Output Standard
- ✓ Latching/Non-Latching Relays
- ✓ Red or Green Display
- ✓ Optional Isolated Analog Output

The CN1000 Series combines the features of a controller, monitor and temperature limit alarm into one easy-to-use digital meter for applications that require maximum versatility. The CN1001TC is selectable for J, K, T or J DIN thermocouple input with 1° resolution. The CN1001RTD is selectable for 100 Ω Platinum RTD inputs (alpha = 0.00385) with 0.1° resolution. Dual independent setpoints are available and are programmable for proportional or on/off operation. The standard analog output is a retransmission of the temperature input and can be sent to a remote chart recorder, data logger or data acquisition system.

Step Response: 2 seconds
Power: 115 or 230 Vac ±10%, 0 to 60 Hz; 8 W max
Isolation: Dielectric strength to 2500V transient per 3 mm (0.12") spacing based on EN61010 for 260 Vrms or DC
NMR: 60 dB
CMR: 120 dB
Input Resistance: 100 MΩ
Operating Temperature: 0 to 50°C (32 to 122°F)

Storage Temperature: -40 to 85°C (-40 to 185°F)
Analog Output: (optional isolated version): scalable 0 to 10 Vdc or 4 to 20 mA
Dimensions: 48 H x 96 W x 152 mm D (1.89 x 3.78 x 6.0")
Panel Cutout: 45 H x 92 mm W (1.772 x 3.622")
Weight: 574 g (1.27 lb)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model No.	Price	Description	Input Type	Range
CN1001TC	\$395	Programmable thermocouple controller	J	-210 to 760°C (-346 to 1400°F)
			J DIN	-270 to 1372°C (-454 to 2500°F)
			T	-210 to 400°C (-346 to 752°F)
			K	-200 to 900°C (-328 to 1652°F)
CN1001RTD	395	Programmable RTD controller	100 Ω Pt 2-, 3-, 4-wire	-200 to 850°C (-328 to 1562°F)

Comes complete with operator's manual.

Ordering Example: CN1001RTD-GN-AI-DC26/56, programmable thermocouple controller, with green display and 26 to 56 Vdc power, and isolated analog output, \$395 + 120 + 10 = \$525.

Display, Output and Power Options

Suffix	Price	Description
-GN	N/C	Green LED display
-AI	\$10	Isolated analog output
-230V	N/C	230 Vac power
-DC10/32	95	10 to 32 Vdc power
-DC26/56	120	26 to 56 Vdc power

Specifications

Input: Thermocouples Type J, K, T, and J DIN

RTD Input: 100 Ω Pt (0.00385 curve) 2-, 3- and 4-wire selectable

Signal Input: 240 Vrms overvoltage protection

Outputs: 2 Form C (SPDT) relays, rated 5 A, 250 Vac; programmable through software for proportional/ non-proportional (on-off) control, or active high/low alarms with latching/nonlatching relays

Relay Hysteresis: Programmable for 0 to 9999

Accuracy: ±0.5% @ 25°C (77°F) after 30-min warm-up

Temperature Coefficient: ±50 PPM/°C

Read Rate: 3/s

Accessories

Model No.	Price	Description
SPC4	\$30	NEMA 4 heavy-duty splashproof lens with screw clamp
SPC18	30	NEMA 4 splashproof lens with spring clip
DPP-5	525	1/8 DIN panel punch



books1.com
 omega.com

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters