

INDUSTRIAL PRESSURE SWITCHES FOR HARSH ENVIRONMENTS

PSW-200 Series Vacuum to 1700 psi

Starts at
\$256



- ✓ Rugged, One-Piece, Epoxy-Coated Aluminum Body
- ✓ Meets NEMA 4X (IP66) Classification
- ✓ UL Listed, cUL Certified
- ✓ Stainless Steel Nameplate
- ✓ Internal Reference Scale with Adjustment Lock
- ✓ Hermetically Sealed SPDT or DPDT Switch

SPECIFICATIONS

Approvals: UL listed, cUL certified

Storage Temperature:
-54 to 71°C (-65 to 160°F)

Ambient Temperature Limits:
-40 to 71°C (-40 to 160°F), except models PSW-234 to PSW-240 and PSW-520 to PSW-525: -18 to 71°C (0 to 160°F); setpoint typically shifts less than 1% of range for a 28°C (50°F) ambient temperature change

Process Temperature:
Stainless Steel: -57 to 204°C (-70 to 400°F)
Phosphor Bronze: -40 to 149°C (-40 to 300°F)
Buna-N: -23 to 93°C (-10 to 200°F)

Shock: Setpoint repeats after 15 g, 10 ms duration

Vibration: Setpoint repeats after 2.5 g, 5 to 500 Hz

Enclosure Classification:
Complies with NEMA 4X (IP66)

Setpoint Repeatability: 1% of adjustable range, except models PSW-241 to PSW-245D: 1.5%

Switch Output: Hermetically sealed SPDT or DPDT switch can be wired "normally open" or "normally closed"

Electrical Output: 11 A, 125/250 Vac resistive

Enclosure: Die-cast aluminum, epoxy coated, gasketed

Weight: 0.7 to 2.7 kg (1.5 to 6 lb) (varies by model)

Electrical Connection: ½ NPT and (2) 22 mm (¾") diameter knockouts

Pressure Connection: ½ FNPT, or ¼ FNPT as noted in "To Order" chart



PSW-236, \$256, shown smaller than actual size.

Dimensions:
psi Ranges:
214 max H x 101 W x 60 mm D
(8.4 max 4 x 2.3")
inH₂O Ranges: W and D = 152 mm (6")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)							
MODEL NO.	PRICE	ADJUSTABLE RANGE		DEADBAND FIXED 0 TO 100 % RANGE	PROOF PRESSURE	SWITCH	ADDED FEATURE
		STANDARD	METRIC				
BUNA-N DIAPHRAGM, O-RING, ¼ NPTF 304 SS PRESSURE CONNECTION							
PSW-234	\$256	3 to 20 psi	0.21 to 1.38 bar	1 to 4 psi	1000 psi	11 A SPDT	—
PSW-234D	296	3 to 20 psi	0.21 to 1.38 bar	3.8 psi typ.	1000 psi	11 A DPDT	DPDT SWITCH
PSW-236	256	3 to 100 psi	0.21 to 6.90 bar	2 to 12 psi	1000 psi	11 A SPDT	—
PSW-236D	296	3 to 100 psi	0.21 to 6.90 bar	11.3 psi typ.	1000 psi	11 A DPDT	DPDT SWITCH
PSW-238	256	15 to 500 psi	1.03 to 34.48 bar	15 to 60 psi	2500 psi	11 A SPDT	—
PSW-238D	296	15 to 500 psi	1.03 to 34.48 bar	26.3 psi typ.	2500 psi	11 A DPDT	DPDT SWITCH
PSW-240	256	100 to 1700 psi	6.90 to 117 bar	20 to 110 psi	2500 psi	11 A SPDT	—
PSW-240D	296	100 to 1700 psi	6.90 to 117 bar	93.8 psi typ.	2500 psi	11 A DPDT	DPDT SWITCH
PHOSPHOR-BRONZE BELLOWS, ¼ NPTF NICKEL-PLATED BRASS PRESSURE CONNECTION							
PSW-246D	\$304	30 inHg vac to 0	-1 to 0 bar	11.3 inHg vac typ.	30 psi	11 A DPDT	DPDT SWITCH

PRESSURE SWITCHES

PSW-241, psi range, \$277, shown smaller than actual size.

See switch accessories on page H-47 for audible alarms and relay modules.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	ADJUSTABLE RANGE		DEADBAND		PROOF PRESSURE	SWITCH	ADDED FEATURE
		STANDARD	METRIC	0 to 75 RANGE	100% RANGE			
WELDED 316 SS DIAPHRAGM, 1/2 NPTF 316 SS PRESSURE CONNECTION								
PSW-231	\$378	1 to 20 psi	0.07 to 1.38 bar	0.1 to 3 psi		500 psi	11 A SPDT	–
PSW-231D	418	1 to 20 psi	0.07 to 1.38 bar	3.8 psi typ.		500 psi	11 A DPDT	DPDT SWITCH
PSW-232	378	2 to 50 psi	0.14 to 3.45 bar	0.1 to 5 psi		500 psi	11 A SPDT	–
PSW-232D	418	2 to 50 psi	0.14 to 3.45 bar	5.3 psi typ.		500 psi	11 A DPDT	DPDT SWITCH
PSW-241	277	5 to 30 psi	0.34 to 2.07 bar	3 to 8 psi	10 psi	2500 psi	11 A SPDT	–
PSW-241D	318	5 to 30 psi	0.34 to 2.07 bar	9.8 psi typ.		2500 psi	11 A DPDT	DPDT SWITCH
PSW-242	277	10 to 100 psi	0.69 to 6.90 bar	3 to 30 psi	45 psi	2500 psi	11 A SPDT	–
PSW-242D	318	10 to 100 psi	0.69 to 6.90 bar	41.3 psi typ.		2500 psi	11 A DPDT	DPDT SWITCH
PSW-243	277	15 to 300 psi	1.03 to 20.69 bar	10 to 40 psi	60 psi	2500 psi	11 A SPDT	–
PSW-243D	318	15 to 300 psi	1.03 to 20.69 bar	52.5 psi typ.		2500 psi	11 A DPDT	DPDT SWITCH
PSW-244	277	20 to 500 psi	1.38 to 34.98 bar	15 to 45 psi	75 psi	2500 psi	11 A SPDT	–
PSW-244D	318	20 to 500 psi	1.38 to 34.98 bar	67.5 psi typ.		2500 psi	11 A DPDT	DPDT SWITCH
PSW-245D	318	80 to 1700 psi	5.50 to 117 bar	168.8 psi typ.		2500 psi	11 A DPDT	DPDT SWITCH
BUNA-N DIAPHRAGM, O-RING WITH 1/2 NPTF ALUMINUM PRESSURE CONNECTION								
PSW-221	\$414	300 vac to 0 inWC	-747.24 to 0 mbar	0.8 to 32 inWC		400 psi	11 A SPDT	–
PSW-221D	454	300 vac to 0 inWC	-747.24 to 0 mbar	36 inWC typ.		400 psi	11 A DPDT	DPDT SWITCH
PSW-222	414	10 vac to 10 inWC	-24.94 to 24.94 mbar	0.4 to 2.4 inWC		400 psi	11 A SPDT	–
PSW-222D	454	10 vac to 10 inWC	-24.94 to 24.94 mbar	2.7 inWC typ.		400 psi	11 A DPDT	DPDT SWITCH
PSW-223	414	50 vac to 50 inWC	-124.54 to 124.54 mbar	0.4 to 12 inWC		400 psi	11 A SPDT	–
PSW-223D	454	50 vac to 50 inWC	-124.54 to 124.54 mbar	13.5 inWC typ.		400 psi	11 A DPDT	DPDT SWITCH
PSW-224	414	0.5 to 5 inWC	1.25 to 12.45 mbar	0.4 to 1.2 inWC		400 psi	11 A SPDT	–
PSW-225	414	2.5 to 50 inWC	6.23 to 124.154 mbar	0.4 to 3.2 inWC		400 psi	11 A SPDT	–
PSW-225D	454	2.5 to 50 inWC	6.23 to 124.154 mbar	3.6 inWC typ.		400 psi	11 A DPDT	DPDT SWITCH
PSW-226	414	10 to 250 inWC	24.91 to 622.70 mbar	0.4 to 24 inWC		400 psi	11 A SPDT	–
PSW-226D	454	10 to 250 inWC	24.91 to 622.70 mbar	27 inWC typ.		400 psi	11 A DPDT	DPDT SWITCH

Comes with complete operator's manual.

Important Note Regarding DPDT Switches: DPDT switches are manufactured so that contact transfer of both switches occurs at the same time for rising pressure setpoints. For falling pressure setpoints, a small amount of non-simultaneity in the switch outputs may be observed. **Note:** Deadbands are fixed and non-adjustable and tend to increase linearly with increased setpoint.

Ordering Example: PSW-241, 5 to 30 psi, stainless steel diaphragm, fixed deadband, \$277.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
MS-1001	\$120	Reference Book: Heating, Ventilating, and Air Conditioning



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters