

Thermistor Meters

Series 860
\$199
 All Models



No Points

Phone plug connector provided FREE with each unit.

865F, \$199, shown smaller than actual size.

- ✓ Comes with Certificate Stating NIST-Traceability
- ✓ Computable with All Series "400" Thermistor Sensors and Probes
- ✓ Rugged
- ✓ 0.1° Resolution
- ✓ Economical and Accurate

Specifications

Sensor: OMEGA® Series 400 Thermistor (2252 Ω @ 25°C); or thermistors with 44004 element

Accuracy: Includes repeatability, temperature coefficient (18 to 28°C ambient), times stability (1 year) and linearization conformity errors; excludes probe errors

Repeatability: 0.1°C (0.2°F) typical for 1 week at constant ambient temperature

Temperature Coefficient: 18 to 28°C (64 to 82°F); included in accuracy specification; less than 18°C (64°F) or greater than 28°C (82°F) less than ± (0.06% rdg + 0.01°C)/°C

Linearization: Ratiometric dual slope A/D with continuous linearization

Mating Connection: ¼" phone jack; model PPM-2

Display: 3½ digit LCD, 13 mm (0.5") height; polarity, decimal point, open sensor and overrange indication

Reading Rate: 1.5 per second

Battery Life: 350 hours typical, with 9 V alkaline battery (included)

Battery Indicator: Display reads "LO BAT" when less than 10% of life remains

Environmental Limits:
Operating: -10 to 50°C (14 to 122°F), less than 80% RH, up to 35°C
Storage: -35 to 60°C (-31 to 140°F), less than 90% RH, up to 35°C

Maximum Common Mode Voltage: 42 V peak

Dimensions: 160 x 69 x 31 mm (6.3 H x 2.7 W x 1.2" D)

Net Weight: 210 g (7.5 oz)

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners

The 865F and 866C thermistor thermometers offer exceptional value combining thermistor accuracy, heavy duty construction and probe interchangeability.



Sensor sold separately. See OMEGA's complete line of thermistor probes and handles in Section D.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)					
Model No.	Price	Setting	Range	Resolution	Accuracy
865F	\$199	200°F	-70.0 to -40.1°F	0.1°F	±(0.3%rdg +1.0°F)
			-40.0 to 199.9°F	0.1°F	±(0.3%rdg +0.5°F)
		300°F	-70 to 300°F	1°F	±(0.3%rdg +1°F)
866C	199	150°C	-55.0 to -40.1°C	0.1°C	±(0.3%rdg +0.6°C)
			-40.0 to 150.0°C	0.1°C	±(0.3%rdg +0.3°C)
Accessories					
Model No.	Price	Description			
CAL-3-HH	\$75	NIST-traceable calibration with points			
SC-800	10	Soft carrying case			
PPM-2	2.50	Extra mating phone plug			
MN1604	3	9 V alkaline battery			
EXPP-2CU-24S-50	39	Extension wire for Series 400 thermistors, 24 gage polyvinyl insulation, 15 m (50')			
OT-201-1/2	5	½ oz jar of high thermal conductivity paste for fast surface measurements			

Comes with battery, operator's manual, and phone plug (PPM-2).

Ordering Example: 865F, thermistor thermometer, in fahrenheit readout, \$199. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$49) \$199 + 49 = \$248.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters