

Thin-Stem Pocket Thermometer

DialTemp™



- ✓ Accurate
- ✓ Quick Response
- ✓ Rugged
- ✓ Shock-Resistant
- ✓ Lightweight
- ✓ Convenient to Use
- ✓ Stainless Steel Construction
- ✓ Sensitive Bi-Metal Element
- ✓ Clear, Easy-to-Read Pointer to Dial
- ✓ Unbreakable Plastic Crystal
- ✓ External Reset Adjustment
- ✓ Waterproof and Dustproof
- ✓ Plastic Pocket Case

K-79 Series
\$20
All Models

This handy little pocket thermometer is great for spot-checking temperatures accurately and quickly. The clear, easy-to-read dial, with a pointer directly driven by the precision sensitive bi-metal helix coil, gives an accurate reading every time. With a head and stem of stainless steel and plastic crystal (no mercury or glass), this thermometer is virtually unbreakable. A plastic pocket case is included, allowing the thermometer to be securely fastened to a pocket, preventing loss, and to be readily accessed. Should the need ever arise for resetting the pointer, an external adjustment feature permits simple zero reset in seconds.

This precision-built thermometer makes checking fluids, gases, or semi-solids quick, easy, and exact. It can be used for testing a multitude of materials in hundreds of fields. Air conditioning, food processing, refrigeration, cookers, frozen foods, chemicals, radiators, meats, fish, fruit, incubators, milk and dairy products, dishwashers, soil, compost, and water represent just a sampling of the applications.

Operating Instructions

Normal Usage:

Insert stem at least 2 inches into fluids and 4 inches into gases to obtain an accurate reading. The thermometer can be handheld in most applications; however, to avoid excessive heat exposure to hand, a "holder-loop" is provided on the clip at the top of the pocket case. Insert the stem through the loop, and the case becomes a holder for the thermometer.

Semi-Solid Materials:

When inserting into semi-solid materials, such as frozen foods, soils, meat, fish, fruit, etc., hold stem firmly and insert slowly and carefully to avoid bending. Do not hold head when inserting—always hold stem.

Specifications

Accuracy: 1% of scale

Head: 25 mm (1") diameter

Dial: White background with crisp letters, marks and numbers

Stem: 3.6 mm OD, 127 mm L (0.142 x 5")

Reset Nut: 11 mm (7/8") hex


Pocket Case: Plastic with clip and holder loop

Weight: 18.6 g (0.65 oz)

Packaging: Individually packaged

Temperature Ranges:

See order chart below for choices



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)					
Model No.	Range	Model No.	Range	Model No.	Range
K-79-2	-40 to 160°F	K-79-4	25 to 125°F	K-79-7	-10 to 110°C
K-79-3	0 to 220°F	K-79-5	50 to 550°F	K-79-8	0 to 150°C

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters