



Portable Dew Point Monitor

RHB-1500 Series Starts at

£3170



- ✓ Primary Field Measurement Technique
- ✓ Accuracy: $\pm 0.2^{\circ}\text{C}$
- ✓ NIST-Traceable
- ✓ Rechargeable Batteries
- ✓ Easily Transportable in Hard Protective Case
- ✓ Wide Measurement Range: -60 to 75°C (-76 to 167°F)
- ✓ Microprocessor Controlled
- ✓ Self-Balancing

RHB-1500-C1S2, £3170, shown smaller than actual size.



This portable dew point hygrometer integrates the accuracy and reliability of the OMEGA[®] chilled mirror with the battery life and ruggedness required for field use.

The RHB-1500-C portable chilled-mirror hygrometer has all the standard features, such as drift-free NIST-traceable accuracy, low maintenance, high durability, and ease of use—in a system that is ideally suited for the demands of field use. Whether you use the RHB-1500-C as a field transfer standard or to spot-check your process air dryness or dew point, you'll find this system provides trouble-free operation.

The RHB-1500-C is a self-contained system. Not only is field assembly not required, but also there is not a need to carry around a myriad of individual components such as control boxes, sensors, cables, pumps, and power cords. Simply attach the sample line, adjust the flow (with the integral flowmeter),

and turn on the power. Within minutes you'll be collecting field dew point data with the same chilled-mirror accuracy of a lab-standard hygrometer. And with a nominal battery life of 12 hours, the RHB-1500-C lets you collect for the entire shift or spot-check your processes for several days.

RHB-1500-C1S2,
£3310, shown smaller
than actual size.



Specifications

Measurement

Range (Dew/Frost Point):

2-Stage (S2):

-40 to 50°C (-40 to 122°F)

3-Stage (S3):

-60 to 50°C (-76 to 122°F)

Accuracy (Dew/Frost Point):

±0.25°C (0.45°F)

Functionality

Power/Charger: 115 to 230 Vac,
50 to 600 Hz

Operating Temperature:

0 to 50°C (32 to 122°F)

Sample Connection:

¼" compression fitting

Sample Flow Rate: 0.5 to 5 SCFH;
integral flowmeter

Sample Pressure:

0 to 150 psig
(higher pressures available; consult
Engineering Department)*

Output:

Analog: 4 to 20 mA (0 to 5 Vdc), -50 to 50°C
(-58 to 122°F) or -60 to 75°C (-76 to 167°F)

Compliance: 9.0 Vdc, 450 Ω

Display: Red LED, 0.5" tall; 8-digit alphanumeric

Alarm:

Visual: Flashing "ALARM" message

Relay: 1 form "C", non-latching; 10 A @ 240 Vac,
8 A @ 24 Vdc, ½HP @ 240 Vac

PHYSICAL

Dimensions: 37.5 H x 46 W x 18 cm D (14.75 x 18 x 7")

Weight: 11 kg (24 lb)

Enclosure: Plastic carrying case

* Unit requires a pump for non-pressurized systems.



STANDARD FEATURES

- ✓ Programmable Automatic Balance Control (ABC)
- ✓ 8-Digit Alphanumeric Display
- ✓ User-Programmable Alarm
- ✓ Visual Alarms
- ✓ 4 to 20 mA (or 0 to 5 Vdc) Analog Output
- ✓ Microprocessor-Controlled
- ✓ 115/230 Vac Battery Charger

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
RHB-1500-C1S2	£3310	Battery powered, 2-stage chill mirror
RHB-1500-C1S2-RHB-ATP	3810	Battery powered, 2-stage chill mirror and temperature probe with 3 m (10') cable
RHB-1500-C1DS2R	3395	Battery powered, 2-stage remote chill mirror
RHB-1500-C1DS2R-RHB-ATP	3895	Battery powered, 2-stage remote chill mirror and temperature probe with 3 m (10') cable
RHB-1500-C1S2L	4730	Line powered, 2-stage chill mirror
RHB-1500-C1S2L-RHB-ATP	3670	Line powered, 2-stage chill mirror and temperature probe with 3 m (10') cable
RHB-1500-C2-3	4995	Line powered, 3-stage chill mirror
RHB-1500-C2-3-RHB-ATP	5495	Line powered, 3-stage chill mirror and temperature probe with 3 m (10') cable
RHB-C2-DS2	3255	Line powered, 2-stage remote chill mirror
RHB-C2-DS2-RHB-ATP	3755	Line powered, 2-stage remote chill mirror and temperature probe with 3 m (10') cable
ES-1501	57	Reference Book: Air Quality

Comes with complete operator's manual and NIST certificate.

Ordering Example: RHB-1500-C1S2, battery-powered hygrometer with 2-stage chill mirror, £3310.

Hu-50

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters