

1/16 DIN Autotune Temperature Controllers



Panel punches available, visit omega.com/panelpunches

CN9000A Series Starts at **\$209**



- ✓ User Selectable Input from 9 Thermocouple Types or RTD Input
- ✓ Clear 3½ Digit High-Brightness Green LED
- ✓ 0.1° Resolution to 200°
- ✓ Constant Setpoint Deviation Indication
- ✓ Auto/Manual Output Control
- ✓ User Select from Autotune PID, PI, PD, P or On/Off Control
- ✓ Independent Second Setpoint and Output Models
- ✓ Comprehensive Alarm Features Deviation, Full Scale, Loop Break with Latching Option
- ✓ Fault Indication for Sensor Burnout, Sensor Short, Heater Break and Process Diagnostics
- ✓ Min/Max Data Storage and Autotune Diagnostics Eliminates Need for Chart Recorder
- ✓ Optional 24 Vac Power
- ✓ Field Replaceable Output Modules

CN9111A, \$230 with KMTSS-125G-6 thermocouple sold separately, \$24. See page A-81. Shown larger than actual size.

changed by the operator at any time, allowing the operator to fine tune the controller to an individual process.

The microprocessor holds all data in non-volatile memory, with the ability to retain data for 10 years with no power. The CN9000A has a large, 3½ digit green LED readout, with auxiliary indicators for each output, and 3 LED's to indicate deviation from setpoint.


Selection of all operational controls is made through the keys on the front panel, with the display prompting the user through each step. After the parameters have been set, they can be locked in, simply by removing a jumper located behind the front bezel. The user can select the control mode and parameters, display resolution (1 or 0.1°), and units (°F/°C). The operator can also utilize the ranging feature, which limits the range in which the setpoint may be chosen, or lock out a user from changing the setpoint. The new single setpoint controller has rear termination. The optional second setpoint and output of the CN9000A model can be set for proportional, on-off or latching limit control, and can be set as either a tracking or non-tracking setpoint. Cycle time, proportional band and on-off deadband are all set independently of the primary setpoint.

Specifications

- Accuracy:** ±0.25% FS ±1°C (0.5°C in 0.1° resolution mode); 30 min warm-up; see also linearized tolerance from range chart
- Control Stability:** ±0.15% FS, typical
- Sample Rate:** 3 per second
- Auto Calibration:** Every 5 s, with re-zero of cold junction compensation
- Temperature Coefficient:** Less than 150 ppm/°C max
- External Resistance:** 100Ω max
- Cold Junction Compensation:** 0.05 degrees/degree ambient typical
- Burnout Protection:** Fault display, upscale/downscale selectable
- Display:** 3½ digit green LED; 10 mm (0.4") high; 1 or 0.1° resolution; error indication, 3 deviation from setpoint indicators
- Setpoint 1:** Selectable between autotune PID, PDPI, PD or on-off
- Setpoint 2 (Optional):** Deviation alarm high or low, "out of limits," or not used; proportional or on-off control; set as up to ±127° deviation from setpoint 1 or full scale (independent PV); high or low process alarm; control output for cooling alarm can be latching for limit control

The CN9000A digital temperature controllers feature high accuracy and reliability, and the sophisticated PID with approach control for optimal control during start-up and steady-state operation. These units are well suited for a broad range of applications, and are easy to install and operate. The unique, sophisticated autotune algorithm will calculate the optimum PID values, and additionally recommends the best value for cycle time. For most applications, the user need only select the desired input type, simply by using the front pushbuttons. The autotune parameters can be

Companion controller CN9500 Series, 1/2 DIN, \$169. See page P-33.



Cycle Time: 0.3, 1, 2, 3, 5, 7, 10, 14, 20, 30, 45, or 60 sec; setpoint 1 or 2

Auto-Tuning: Unit determines proportional band, integral and derivative values, and suggests optimal cycle time (setpoint 1 only)

Proportional Band: 0.5, 1, 1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10, 14, 20 or 100% of span (setpoint 1 or 2)

Derivative (Rate): Off, 1, 2, 3, 5, 10, 15, 20, 25, 35, 50, 75, 100, or 200 s; AT value

Integral (Auto Reset): Off, 0.2, 0.5, 1, 2, 3, 5, 7, 10, 13, 18, 25, 33, 43, or 600 min

Approach Control: Off, 0.5, 1, 1.5, 2, 2.5, 3, 4, or 5 times proportional band

Manual Reset: PD, proportional and on-off control; set as degrees deviation from setpoint 1

On-Off Deadband: 0.25, 0.5, 0.75, 1, 1.25, 1.5, 2, 2.5, 3, 4, 5, 7, 10 or 50% FS (setpoint 1 or 2)

Power: 24 Vac, 115 Vac, 230 Vac, ±15%, 50 to 60 Hz

Power Consumption: 6 VA

Output 1 Relay: SPDT relay, 5 A @ 250 Vac

Output 2 Relay: SPDT relay, 3 A @ 250 Vac

dc Pulse Output: Non-isolated 5 Vdc pulse for driving external DC solid state relay

Common Mode Noise Rejection: 140 dB, 240 Vac, 50/60 Hz

Normal Mode Noise Rejection: 60 dB, 50 Hz

Ambient Operating Range: 4 to 50°C (40 to 122°F)

Dimensions:

48 H x 48 W x 13 mm D bezel (1.89 x 1.89 x 0.5"); 115 mm (4.5") depth behind panel; 154 mm (6.1") with triac voltage or current output

Panel Cutout: 45 mm square (1.772"); 1/16 DIN

Weight: 0.38 kg (0.84 lb)

Input Types and Ranges

Input Type	Linearized Range (Units are °F/°C Switchable)	Linearized Tolerance	Preset Span*
J	32 to 1470°F 0 to 800°C	1°C/2°F	400°C
K	32 to 1999°F 0 to 1200°C	1°C/2°F	400°C
T	-199 to 500°F -199 to 250°C	2°C/4°F	250°C
E	32 to 1100°F 0 to 600°C	1°C/2°F	500°C
R	32 to 572°F 572 to 1999°F	5°C/9°F 2°C/4°F	1600°C
S	32 to 572°F 572 to 1999°F	5°C/9°F 2°C/4°F	1600°C
B	1000 to 1999°F 500 to 1800°C	6°C/11°F	1600°C
N	32 to 1999°F 0 to 1200°C	1°C/2°F	400°C
L (J DIN)	32 to 1470°F 0 to 800°C	1°C/2°F	400°C
RTD	-199 to 750°F -199 to 400°C	0.5°C/0.9°F	200°C

* User adjustable limit on setpoint.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Input	Output 1	Output 2
CN9110A	\$209	T/C, 2-wire RTD	Relay	—
CN9111A	230		Relay	Relay
CN9112A	230		Relay	Pulse
CN9120A	209		Pulse	—
CN9121A	230		Pulse	Relay
CN9122A	230		Pulse	Pulse
CN9131A	293		1 A SSR	Relay
CN9141A	293		4 to 20 mA	Relay
CN9151A	293		0 to 10 Vdc	Relay
CN9210A	209		3-wire RTD	Relay
CN9211A	230	Relay		Relay
CN9212A	230	Relay		Pulse
CN9220A	209	Pulse		—
CN9221A	230	Pulse		Relay
CN9222A	230	Pulse		Pulse
CN9231A	293	1 A SSR		Relay
CN9241A	293	4 to 20 mA		Relay
CN9251A	293	0 to 10 Vdc		Relay

Accessories and Replacement Output Modules

Model No.	Price	Description
CN9000-14	\$10	1/4 DIN mounting adaptor
CN9000-18	10	1/8 DIN mounting adaptor
CN9000A-SOCKET	17	Terminal socket
BD9011A	32	Dual relay, field installable module
BD9021A	25	Pulse/relay, field installable module
BD9031A	65	1 A SSR and relay, field installable module
BD9041A†	65	4 to 20 mA and relay, field installable module
BD9051A†	65	0 to 10 Vdc and relay field installable module
BD9010A	32	Relay output board
BD9012A	40	Relay/pulse field installable module
BD9022A	27	Dual pulse field installable module
DPP-4	475	1/16 DIN panel punch

For Additional Controllers and Indicators, See Section M

Comes complete with operator's manual.

† For 230 Vac powered boards add suffix "-230V" to model number, no additional charge.

115 Vac models are UL recognized. UL not available for 230 Vac models.

For 230 Vac power, add suffix "-230VAC" to model number, no additional charge. For 24 Vac power, add suffix "-24VAC" to model number, no additional charge.

Ordering Examples: CN9121A, autotune controller with thermocouple/2-wire RTD input, pulse output (output 1) and relay output (output 2), with CN9000-14 (1/4 DIN mounting adaptor), \$230 + 10 = \$240.

OCW-2 OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$43), \$240 + 43 = \$283.

CN9210A, autotune controller with 3-wire RTD input, relay output (output 1), \$209.

BD9011A, replacement output board, dual relay module, \$32.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor, and equivalent loaners.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters