



1/8 DIN Digital Panel RTD Meters

DP63200-RTD

\$186

Panel Punches Available, Visit omega.com/panelpunches



DP63200-RTD, \$186, shown actual size.

- ✓ RTD Meter
- ✓ 4-Digit, 14.2 mm (0.56") LED
- ✓ Accepts Standard 3-Wire 100 Ω RTD Sensors (ALPHA = 0.00385 or ALPHA = 0.00392)
- ✓ Conforms to ITS-90 Standards
- ✓ Selectable °F or °C with 0.1 or 1 Degree Display Resolution
- ✓ Programmable Temperature Offset
- ✓ Programmable Digital Filtering
- ✓ Peak/Valley (High/Low Reading) Memory
- ✓ NEMA 4X (IP65) Sealed Front Bezel
- ✓ Custom Units Overlay with Backlight

The DP63000-RTD meter accepts standard RTD inputs and precisely linearizes them into temperature readings. A full 4-digit display accommodates a wide range of temperature inputs. State-of-the-art digital circuitry virtually eliminates errors due to drift. The meter features a readout choice of either Fahrenheit or Celsius with 0.1 or 1° resolution. Display prompts and front panel buttons aid the operator through set-up and operation. Programmable digital filtering enhances the stability of the reading. All set-up data is stored in EEPROM, which will hold data for a minimum of 10 years without power. The meter provides a peak "HI" and valley "LO" reading memory with selectable capture delay time. The capture delay is used to prevent detection of false peak or valley readings that may occur during start-up or unusual process events. The peak and valley readings are

stored at power-down, allowing process limits to be monitored over any length of time. The meter has several built-in diagnostic functions to alert operators of any malfunction. Extensive testing of noise interference mechanisms and full burn-in makes the meter extremely reliable in industrial environments. The front bezel meets NEMA 4X (IP65) requirements for wash-down applications.

Specifications

Display: 4-digit, 14.2 mm H (0.56") LED, minus sign displayed for negative temperatures
Power: 85 to 250 Vac, 50/60 Hz, 6 VA
Isolation: 2300 Vrms for 1 minute between input and supply (300V working voltage)
Resolution: 0.1 or 1°
Range (Decimal Point Dependent):
 0.1° Res: -199.9 to 850.0°C (-199.9 to 999.9°F)
 1° Res: -200 to 850°C (-328 to 1562 °F)
Lead Resistance Effect: 20 Ω max, 2.5 °C/Ω error for V exc and common lead unbalance
Accuracy: 0.3°C, @ 23°C and 30 minute warm-up

Reading Rate: 2.5 readings/s
Response Time: 2 s to settle for step input (increases with programmable digital filtering)
Low-Frequency Noise Rejection:
Normal Mode Rejection: 40 dB @ 50/60 Hz (may be improved by programmable digital filtering)
Common Mode Rejection: 120 dB, DC to 50/60 Hz
Environmental Conditions:
Operating Temperature Range: 0 to 50°C (32 to 122°F)
Storage Temperature Range: -40 to 80°C (-40 to 176°F)
Operating and Storage Humidity: 85% max RH non-condensing from 0 to 50°C (32 to 122°F)
Span Drift: 50 ppm/°C
Zero Drift: 0.001°C/°C
Altitude: Up to 2000 m (6562')
Construction: This unit is rated for NEMA 4X (IP65) indoor use, 1 piece bezel/case, flame-resistant—panel gasket and mounting clip included
Connections: High-compression, cage-clamp terminal block
Dimensions: 104.1 D x 91.4 W x 44.5 mm H (4.10 x 3.50 x 1.75)
Weight: 0.24 kg (0.65 lb)

AVAILABLE FOR FAST DELIVERY

To Order (Specify Model Number)

Model No.	Price	Description
DP63200-RTD	\$186	RTD input, 85 to 250 Vac, 50/60 Hz

Comes complete with operator's manual.

Ordering Example: DP63200-RTD, RTD input, 85 to 250 Vac, 50/60 Hz, \$186.

Accessories

Model No.	Price	Description
DPP-5	\$525	1/8 DIN panel punch
EE-1319	85	Reference Book: Grounding and Shielding Techniques 

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters