

NEW

MULTIFUNCTION TOTALIZERS WITH BATCH CONTROL

DPF708/DPF808 Series Starts at \$209



- Modularized Construction
- Dual 4-Digit LED
- Output and Alarm Status Indicators
- Temperature or Pressure Compensation on DPF800 Series

The DPF708/808 series flow totalizers can accumulate the mass, volume or length of an object, and can provide batch control over the accumulation. The DPF708 series has a single input available in frequency, voltage or current input models. The DPF808 series has an additional input that is available in voltage, current or direct temperature sensor input versions. Abundant functions such as retransmission, high/low alarm of momentary flow and abnormal signal detecting. The DPF808 series also has the ability to trigger alarms for pressure or temperature. Square root function is selectable, 8-digits of accumulation value and 4-digits momentary process value, small signal cut-out can be set at any range.

The DPF808 series has temperature and pressure compensation used for general gas, saturated steam, superheated steam or liquids. The compensation calculation is done with standard look-up tables for high accuracy in steam measurement applications. Advanced computation algorithms insure accuracy in flow measurements. Used as a batch controller, it has 4-bit accumulator for control and a separate 12-bit accumulator for total sum. With high precision current input models, the totalizer can provide retransmission with 14 bit output resolution and 0.2%FS output precision.

TECHNICAL SPECIFICATION

Frequency Input: 0 to 3200 Hz
Temperature (DPF808 series): J, K or E thermocouple, 1 to 5, 0 to 5 Vdc or 4 to 20 mA
Pressure (DPF808 Series): 1 to 5, 0 to 5 Vdc or 4 to 20 mA



Accumulation Time: Fixed at 1 hour for flow accumulation, and the unit can be freely set for batch control.

Frequency Input Models: 0 to 3200Hz, the low level signal is 0 to 1V, the high level signal is 3 to 24V

Voltage Input Models: 1 to 5 V, 0 to 5 V, providing 24 Vdc/24 mA power output

Current Input Models: 4 to 20 mA, 0 to 20 mA, 0 to 10 mA

Temperature Input (DPF808 Series): K (0 to 999°C), E (0 to 800°C), J (0 to 999°C) RTD Pt100 (-200 to 600°C)

Pressure Input (DPF808): 1 to 5 Vdc, 0 to 5 Vdc

Current Input (DPF808): 4 to 20 mA, 0 to 20 mA

Current Output: 4 to 20 mA

Measurement Accuracy: ±0.2% FS, for temperature, pressure, frequency, and momentary flow without temperature or pressure compensation.

DPF828-R1-R2, \$319, shown close to actual size.

Temperature/Pressure Compensation Method (DPF808 Series):

General Gas: Temperature-pressure compensation (calculated with ideal gas equation)

Saturated Steam: Temperature or pressure compensation (calculated with steam tables)

Calculation Accuracy for Temperature-Pressure Compensation: The calculation error is <0.3% FS, and after compensation, the overall error is <0.5% FS

Accumulation Accuracy: The error is <0.01% FS

Power Supply: 100 to 240 Vac, -15%, +10%/50 to 60Hz; or 24 Vdc/Vac, -15% (optional)

Power Consumption: 5 W

Operating Ambient: Temperature -10 to 60 C; humidity 90% RH

SIZE	FRONT PANEL		CUT OUT		DEPTH BEHIND MOUNTING SURFACE (mm)
	WIDTH (mm)	HEIGHT (mm)	WIDTH (mm)	HEIGHT (mm)	
1/8 DIN Vertical	48	96	45	92	100
1/8 DIN Horizontal	96	48	92	45	100
1/4 DIN	96	96	92	92	100

NEW

DPF738-DC1-DC2,
\$209, shown smaller
than actual size.

DPF828-DC1-DC2,
\$319, shown smaller
than actual size.



To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NUMBER	PRICE	DESCRIPTION
DPF708 SERIES		
DPF718*-DC1-DC2	\$209	¼ DIN totalizer, 2 DC pulse outputs
DPF718*-DC1-R2	209	¼ DIN totalizer, DC pulse and relay outputs
DPF718*-R1-R2	209	¼ DIN totalizer, 2 relay outputs
DPF728*-DC1-DC2	219	¼ DIN totalizer, 2 DC pulse outputs with bar graph
DPF728*-DC1-R2	219	¼ DIN totalizer, DC pulse and relay outputs with bar graph
DPF728*-R1-R2	219	¼ DIN totalizer, 2 relay outputs with bar graph
DPF738*-DC1-DC2	209	½ DIN vertical totalizer, 2 DC pulse outputs
DPF738*-DC1-R2	209	½ DIN vertical totalizer, DC pulse and relay outputs
DPF738*-R1-R2	209	½ DIN vertical totalizer, 2 relay outputs
DPF748*-DC1-DC2	209	½ DIN horizontal totalizer, 2 DC pulse outputs
DPF748*-DC1-R2	209	½ DIN horizontal totalizer, DC pulse and relay outputs
DPF748*-R1-R2	209	½ DIN horizontal totalizer, 2 relay outputs
DPF808 SERIES		
DPF818**-DC1-DC2	\$299	Dual input ¼ DIN totalizer, 2 DC pulse outputs
DPF818**-DC1-R2	299	Dual input ¼ DIN totalizer, DC pulse and relay outputs
DPF818**-R1-R2	299	Dual input ¼ DIN totalizer, 2 relay outputs
DPF828**-DC1-DC2	319	Dual input ¼ DIN totalizer, 2 DC pulse outputs with bar graph
DPF828**-DC1-R2	319	Dual input ¼ DIN totalizer, DC pulse and relay outputs with bar graph
DPF828**-R1-R2	319	Dual input ¼ DIN totalizer, 2 relay outputs with bar graph
DPF838**-DC1-DC2	299	Dual input ½ DIN vertical totalizer, 2 DC pulse outputs
DPF838**-DC1-R2	299	Dual input ½ DIN vertical totalizer, DC pulse and relay outputs
DPF838**-R1-R2	299	Dual input ½ DIN vertical totalizer, 2 relay outputs
DPF848**-DC1-DC2	299	Dual input ½ DIN horizontal totalizer, 2 DC pulse outputs
DPF848**-DC1-R2	299	Dual input ½ DIN horizontal totalizer, DC pulse and relay outputs
DPF848**-R1-R2	299	Dual input ½ DIN horizontal totalizer, 2 relay outputs

Comes with mounting hardware and user's manual.

Ordering Example: DPF718F-R1-R2, batch controller with frequency input and 2 relay outputs, \$209.

* Insert input code: "F" (frequency), "V" (voltage) or "C" (current).

** Insert dual input code: "FT" (frequency/temperature), "FC" (frequency/current), "VT" (voltage/temperature), "VC" (voltage/current), "CT" (current/temperature) or "CC" (current/current).

For models with 24 Vdc power add "-24V" to the model number and \$10 to the price.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters