

# POLYCARBONATE ENCLOSURES FOR CIRCUIT BREAKERS AND ELECTRICAL COMPONENTS

EK Series



- NEMA 4X (IP65)
- 35 mm DIN Rail and Label Included
- Tinted Transparent Hinged Door
- Direct Mount
- Corrosion and Maintenance Free
- High Mechanical Strength
- Integral Polyurethane Seals
- Temperature Rated -40 to 120°C (-40 to 248°F)


The EK Series polycarbonate enclosures are a unique design to house and protect standard IEC components, such as DIN rail mount circuit breakers, timers, switches, meters and other control devices. The unique cover design features a shrouded cut-out and transparent hinged doors with push release doors latches, for quick access and visibility. The shrouded cut-out, spanning the width of the cover, exposes mounted components for easy adjustment and isolates wiring for increased safety.




EK012 enclosure 12-poles.



EK008 enclosure 8-poles.



EK002 enclosure 2 to 3 poles, shown with AU-2BU10R 2-pole supplementary protector (sold separately). To order visit [omega.com/enclosures](http://omega.com/enclosures)



DIMENSIONS						
MODEL NO.	# CIRCUIT BREAKER POLES	HEIGHT (A) mm (inch)	WIDTH (B) mm (inch)	DEPTH (C) mm (inch)	CUT-OUT WIDTH (D) mm (inch)	CUT-OUT HEIGHT (E) mm (inch)
EK002	2 to 3*	130 (5.12)	94 (3.70)	93 (3.66)	36 (1.42)	46 (1.81)
EK004	4	180 (7.09)	110 (4.33)	123 (4.84)	72 (2.83)	46 (1.81)
EK008	8	180 (7.09)	180 (7.17)	123 (4.84)	144 (5.67)	46 (1.81)
EK012	12	180 (7.09)	254 (10)	123 (4.84)	216 (8.50)	46 (1.81)
EK024**	24	361 (14.22)	254 (10)	123 (4.84)	216 (8.50)	46 (1.81)

\* Can fit 3-pole with breakouts removed. \*\* 2-door model like 2-stacked EK012

## To Order Visit [omega.com/ek](http://omega.com/ek) for Pricing and Details

MODEL NO.	DESCRIPTION
EK002	NEMA 4X (IP65) enclosure for IEC electrical components, fits 2 or 3 circuit breaker poles
EK004	NEMA 4X (IP65) enclosure for IEC electrical components, fits 4 circuit breaker poles
EK008	NEMA 4X (IP65) enclosure for IEC electrical components, fits 8 circuit breaker poles
EK012	NEMA 4X (IP65) enclosure for IEC electrical components, fits 12 circuit breaker poles
EK024	NEMA 4X (IP65) enclosure for IEC electrical components, fits 24 circuit breaker poles

Comes complete with 35 x 7.5 mm DIN rail and label included.

**Ordering Examples:** EK002, polycarbonate enclosure for DIN mounted IEC components, fits one 2 or 3-pole circuit breaker.

EK008, polycarbonate enclosure with translucent hinged door with latch, for DIN mounted IEC components, fit equivalent of 8 poles.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters