

UNIVERSAL REMOTE I/O MODULES, DIN RAIL MOUNTABLE MODBUS® I/O



HE359 Series
Starts at
\$200



- Connects Via 2-Wire RS485 MODBUS RTU to Any Programmable Logic Controller (PLC)
- A Total of 31 I/O Modules May be Daisy-Chaind on a Single RS485 Link
- Optical Isolation
- Response Time Suitable For Most Analog Applications
- Cost Effective Addition Per Point
- Fits in the Smallest Panels: 17.5 x 100 x 120 mm (0.69 x 3.94 x 4.72")
- 12 Different I/O Modules Including:
 - DC In, DC Out
 - DC In, Relay Out
 - Analog In, Analog Out
 - RTD
 - Thermocouple



(L to R) HE359DAC007, \$280, HE359ADC107, \$245, and HE359RTD100, \$280.

Shown smaller than actual size.

Remote I/O, or distributed I/O, offers several advantages over the traditional local I/O found on a Programmable Logic Controller (PLC). First, it allows you to locate the I/O modules close to the process that is being monitored or controlled. This greatly improves noise immunity, as the weak sensor signals are converted to digital signals before being transmitted long distances through a noisy plant environment. OMEGA universal remote I/O modules use a simple 2-wire RS485 link using MODBUS RTU protocol, which is supported by most programmable logic controllers. A second advantage is that remote I/O greatly reduces the wiring at the main control panel, saving time and money when repairs and upgrades are necessary. Adding additional sensors and control signals is as easy as connecting to the already installed RS485 link and modifying the PLC program to utilize the new I/O. In addition, remote I/O allows you to expand your process control system beyond the local I/O capabilities of your PLC. You can add thermocouple, RTD, pressure, and flow sensors to a PLC that doesn't support these types of inputs. With remote I/O, your process application is no longer dependent on your controller choice.

SPECIFICATIONS

Number of Channels:

- 4: HE359ADC107, HE359ADC120, HE359DAC007, HE359RTD100, HE359THM100, HE359DIQ512
- 8: HE359ADC207, HE359ADV220, HE359DAC107, HE359DAC201, HE359THM200
- 12: HE359DIM610

Input Ranges:

- ±10V: HE359ADC107, HE359ADC207
- ±20 mA: HE359ADC120, HE359ADV220
- 12/24 Vdc: HE359DIM610, HE359DIQ512
- RTD Pt-100, Ni-100, Pt-1000, Ni-1000; 0 to 2000 Ω, 0 to 500 Ω: HE359RTD100
- J, K, R, S, B, E, T, N; ±50 mV, ±100 mV, ±500 mV, ±1V: HE359THM100, HE359THM200

Output Ranges:

- 0 to 20 mA or 0 to 10V: HE359DAC007, HE359DAC107
- 0 to 10V: HE359DAC201

OFF Voltage Level: 0 to 3 Vdc (HE359DIM610, HE359DIQ512)

ON Voltage Level: 10 to 30 Vdc (HE359DIM610, HE359DIQ512)

Resolution:

- 16-bit: HE359ADC107, HE359ADC207, HE359ADC120, HE359ADC220
- 1 μA or 1 mV: HE359DAC007, HE359DAC107
- 1 mV: HE359DAC201
- 0.1°C or 0.1 Ω: HE359RTD100
- 0.1°C or 0.001 mV: HE359THM100, HE359THM200

RTD Excitation Current (HE359RTD100): 350 μA, typical

Accuracy:

- ±0.1% FS: HE359RTD100, HE359THM100, HE359THM200

Load Resistance:

- Voltage: >5 kΩ (HE359DAC007, HE359DAC107, HE359DAC201)
- Current: <500 Ω (HE359DAC007, HE359DAC107)

Output Calibration:

- Voltage: ±10 mV (HE359DAC007, HE359DAC107, HE359DAC201)
- Current: ±20 μA (HE359DAC007, HE359DAC107)

Input Impedance:

- 1 MΩ: HE359ADC107, HE359ADC207
- <50 Ω: HE359ADC120, HE359ADC220
- 4.7 kΩ: HE359DIM610, HE359DIQ512
- >10 MΩ: HE359THM100, HE359THM200

Relay Outputs Per Module (HE359DIQ512): 4 (2 SPDT, 2 SPST)

Max Switching Power (HE359DIQ512): 2A @ 250 Vac, 2A @ 30 Vdc

Min Load (HE359DIQ512): 5 Vdc, 10 mA

Max Voltage (HE359DIQ512): 250 Vac, 110 Vdc

Linearity: ±0.1%

External Power Supply Voltage:

- 10 to 30 Vdc: HE359ADC107, HE359ADC207, HE359ADC120, HE359ADC220, HE359DIM610, HE359RTD100, HE359THM100, HE359THM200
- 18 to 30 Vdc: HE359DAC007, HE359DAC107, HE359DAC201

Required Power (Steady State):

- 30 mA @ 24 Vdc, Typical: HE359ADC107, HE359ADC207, HE359ADC120, HE359ADC220, HE359DAC201, HE359RTD100, HE359THM100, HE359THM200
- 30 mA @ 24 Vdc, Typical (100 mA max): HE359DAC007, HE359DAC107
- 35 mA @ 24 Vdc, Typical: HE359DIM610
- 45 mA @ 24 Vdc, Typical: HE359DIQ512

Required Power (Inrush): Negligible

Isolation: 2000 Vac for 60 seconds (input/power and input/comms)

PLC Update Rate:

- Determined by Communications with OCS: HE359DIM610, HE359RTD100, HE359THM100, HE359THM200
- 20 mS min: HE359DIQ512

Thermal Drift (HE359DAC201): 100 ppm max


Terminal Type: Screw type, removable

Storage Temperature: -40 to 85°C (-40 to 185°F)

Operating Temperature: -10 to 60°C (14 to 140°F)

Relative Humidity (Non-Condensing):

- 5 to 95%: HE359ADC107, HE359ADC207, HE359DAC007, HE359DAC107, HE359DAC201, HE359DIM610, HE359DIQ512, HE359RTD100, HE359THM100, HE359THM200
- 5 to 90%: HE359ADC120, HE359ADC220



Dimensions: 17.5 W x 100 H x 120 mm D (0.69 x 3.94 x 4.72")

Weight: 150 g (6 oz); 210 g (8.4 oz) HE359DIQ512 only

Communications: Modbus/RTU (binary) RS485 half duplex

Default Communications Parameters:

38400 baud, N, 8, 1, no h/s default modbus ID 1

Supported Modbus Commands: 1, 2, 3, 4, 5, 6, 8, 15, 16

Accessories

| MODEL NO. | PRICE | DESCRIPTION |
|-------------------|---------------|---|
| XBANS3575P | \$9.00 | DIN rail, 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6'), slotted |
| XBANS3575U | 9.30 | DIN rail, 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6'), solid |
| XBANS3515P | 17.00 | DIN rail, 35 x 15 mm x 2 m (1.4 x 0.30" x 6.6'), slotted |
| XBANS3515U | 17.00 | DIN rail, 35 x 15 mm x 2 m (1.4 x 0.30" x 6.6'), solid |
| ELC-PS01 | 36.00 | ELC power supply, 24 W, 1 A |
| ELC-PS02 | 71.00 | ELC power supply, 24 W, 2 A |

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

| MODEL NO. | PRICE | DESCRIPTION |
|--------------------|--------------|--|
| HE359DIQ512 | \$200 | I/O module, 4 DC inputs (12/24 Vdc), 4 relay outputs (250 Vac, 30 Vdc, 2A max) |
| HE359DIM610 | 245 | I/O module, 12 DC inputs (12/24 Vdc) |
| HE359ADC107 | 245 | I/O module, 4 analog inputs, voltage (±10 Vdc), 1 mV resolution |
| HE359ADC120 | 245 | I/O module, 4 analog inputs, current (4 to 20 mA), 1µA resolution |
| HE359ADC207 | 385 | I/O module, 8 analog inputs, voltage (±10 Vdc), 1 mV resolution |
| HE359ADC220 | 385 | I/O module, 8 analog inputs, current (4 to 20 mA), 1µA resolution |
| HE359RTD100 | 280 | I/O module, 4 RTD inputs (Pt-100, Ni-100, Pt-1000, Ni-1000) or resistance inputs (0 to 2000 Ω), 0.1°C resolution |
| HE359THM100 | 280 | I/O module, 4 thermocouple inputs (Types J, K, R, S, B, E, T, N) or millivolt inputs (±1000 mV, max), 0.1°C resolution |
| HE359THM200 | 425 | I/O module, 8 thermocouple inputs (Types J, K, R, S, B, E, T, N) or millivolt inputs (±1000 mV, max), 0.1°C resolution |
| HE359DAC007 | 280 | I/O module, 2 analog outputs, selectable between voltage (0 to 10 Vdc) and current (0 to 20 mA), 1 mV/1 µA resolution |
| HE359DAC107 | 425 | I/O module, 4 analog outputs, selectable between voltage (0 to 10 Vdc) and current (0 to 20 mA), 1 mV/1 µA resolution |
| HE359DAC201 | 560 | I/O module, 8 analog outputs, voltage (0 to 10 Vdc), 1 mV resolution |

Ordering Examples: HE359THM100, I/O module, 4 thermocouple inputs, \$280. HE359RTD100, I/O module, 4 RTD inputs, \$280.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters