



# Thin Film Detector (TFD) OMEGA® Thin Film RTD Elements and Probes

TFD Series  
Starts at  
**£16<sup>75</sup>**

This flat Platinum resistance detector represents OMEGA's latest development in miniature temperature sensing devices. It combines the precision of the Platinum resistance detector with the small temperature-sensing tip and rapid response time of the thermocouple. An immediate field of application for the TFD is surface temperature measurement.

The TFD achieves rapid response times because:

- 1) It has a high ratio of surface area to volume
- 2) The temperature-sensitive Platinum layer is separated from the medium to be measured by a thin ceramic substrate of high thermal conductivity.

This is of particular interest to users measuring temperature in gaseous environments, such as wind tunnels and air conditioners. The TFD is also extremely vibration-resistant.

The resistance values and tolerances comply with DIN 43760 and BS 1904 ratings (Pt100).

The TFD element is supplied in an encapsulated sensor screw-mounted brass housing with PFA insulated leads. Two-, 3- or 4- wire configuration is available. Sensor design provides cost effective, fast response and easy mounting on flat surfaces. The maximum temperature of the probe assembly is 260°C (500°F). Termination options are available for easy operation in conjunction with OMEGA handheld meters or other instruments.




## Specifications

**Element:** TFD-design glass-encapsulated Platinum layer on a ceramic substrate

**TFD Leads:** Platinum wire 0.2 mm D (0.008"), about 10 mm L (0.39")

**Temperature Range:**  
-70 to 500°C (-95 to 930°F)

**Insulative Resistance at 500°C (930°F):** >10<sup>8</sup>



**Voltage Necessary for Destruction:** 100 Vdc

**Hysteresis Error (Observed Only after Rapid Temperature Cycling):** Max 0.25  
**Self-Heating Error at 20°C (70°F):**  
In still air, 1.9 mW/°C;  
in still water, 75 mW/°C

**Response Time:**  
**In Water Moving at 0.4 m/s:**  
t(50%) = 0.25 s  
t(90%) = 1.1 s  
**In Air Moving at 1 m/s**  
t(50%) = 13.5 s  
t(90%) = 55 s

**ALL MODELS IN STOCK FOR FAST DELIVERY!**

To Order (Specify Model Number)				
TFD Element				
Model No.	Price	Description		
TFD	£16.75	Thin film RTD element		
Surface Mount Probe				
Model No.	Price	Lead Wire Style	Cable	Price Add'l metre Lead Wire
TFD-ENB-2W-40	£43.50	2 Wires	1 m (40") PFA insulated	£3.00
TFD-ENB-3W-40	43.50	3 Wires	1 m (40") PFA insulated	4.90
TFD-ENB-4W-40	50.00	4 Wires	1 m (40") PFA insulated	4.90

For lead wire length over 1 m, use additional price per metre increments and modify model number.

Ordering Example: TFD-ENB-3W-5M, sensor, screw mounted, 3 wires, 5 metre cable, £63.10.



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters