

INDUCTIVE PROXIMITY SENSOR

iPROX™ OUR HIGHEST PERFORMANCE SENSOR

12, 18 AND 30 mm DIAMETER



iPROX Series
Starts at
£43



- Available in AC 2-Wire, DC 3-Wire
- Reliably Detects Metal Targets at up to 3 Times the Range of Conventional Shielded or Unshielded Tubular Inductive Sensors
- Quality Construction Using a Stainless Steel Barrel, 360° Dual-Colour LED Indicator, Ryton® Impact-Resistant Face Cap and Vibration Absorbing Potting Compound
- Auto-Configuration Technology Automatically Detects a Sinking (NPN) or Sourcing (PNP) Connection and Switches the Sensor Accordingly, Without any User Intervention
- Highly Visible Dual Colour Output Status LED
- Withstands High Electrical Noise (up to 20 V/m)
- Resistant to Extreme Temperatures (-40°C)



E59-M12C110C02-D1, £43, shown bigger than actual size.

TYPICAL APPLICATIONS

- Automotive
- Machine Tool
- Material Handling
- Metalworking

SPECIFICATIONS

2-WIRE SENSORS
Input Voltage: 20 to 132 Vac
Load Current: 12 mm: 5 to 300 mA; 200 mA >50°C
Leakage Current: 1.7 mA @ 0°C, 2.0 mA @ -40°C
Voltage Drop: <5 Vac
Protection: None
Switching Hysteresis: <15% rated sensing distance
Repeat Accuracy
Shielded Models: <1% sensing distance
Unshielded Models: <3% sensing distance
Surge Capacity: 3A/30 ms
Temperature Range: -40 to 70°C
Material of Construction: 303 SS; End bells: Polycarbonate; Face caps: Ryton®; Cable: AWM Style 20387 (PVC)
Vibration and Shock: 10 to 55 Hz, 1 mm Amplitude, IEC 60068-2-6; Shock: 30g, 11 ms per IEC 68-2-27
Indicator LED: 360° viewable LED
Enclosure Ratings: IP67, NEMA 4, 4X, 6, 6P, 12 and 13
Response Time 2-Wire Sensors:
Factory Default Mode: Shipped in “side by side mode” by default (20 V/m)
Side by Side: 30 Hz (10 V/m)
High Noise Immunity Mode: 10 Hz (>20 V/m)

The Cutler-Hammer® iProx represents the highest performance, most versatile tubular inductive sensor offered by Omega. By utilizing an embedded microprocessor and exclusive SmartSense™ technology, iProx can sense up to three times farther than typical sensors of its class. Both shielded and unshielded versions of iProx feature extended sensing ranges. This allows the sensor to be mounted farther from the target, thereby reducing the potential for target impacts and increasing the sensing reliability of your application. With extended sensing range, quality construction and the ability to automatically configure its output for sinking or sourcing connection, iProx is the ideal choice for even the most demanding inductive sensing applications.

Sensors, Pushbuttons and Lights




3-WIRE SENSORS

Input Voltage: AC 6 to 48 Vdc
Load Current: 500 mA @ 6 to 30 Vdc;
 300 mA @ 32 to 48 Vdc
Leakage Current: 150 µA
Voltage Drop: 2.5 Vdc
Burden Current: 15 mA
Protection: Auto Reset
Switching Hysteresis:
 <15% rated sensing distance
Repeat Accuracy:
Shielded Models: <1% sensing distance
Unshielded Models:
 < 3% sensing distance

Temperature Range: -40 to 70°C
Material of Construction: 303 SS;
 End bells: Polycarbonate; Face caps:
 Ryton®; Cable: AWM Style 20387 (PVC)
Vibration and Shock Vibration: 10 to 55Hz,
 1 mm Amplitude, IEC 60068-2-6; Shock:
 30g, 11 mS per IEC 68-2-27
Indicator LED: 360° viewable LED
Enclosure Ratings: IP67, NEMA 4, 4X, 6,
 6P, 12 and 13

Response Time 3-Wire Sensors:
Factory Default Mode:
Shielded:
12 mm: 580 Hz (10 V/m)
18 mm: 390 Hz (10 V/m)
30 mm: 240 Hz (10 V/m)
Unshielded:
12 mm: 300 Hz (10 V/m)
18 mm: 150 Hz (10 V/m)
30 mm: 145 Hz (10 V/m)
Side by Side: 50 Hz (20 V/m)
High Noise Immunity Mode:
 10 Hz (>20 V/m)

Cable Models



SIZE	SHIELDING	A	B	C	D
12 mm	Shielded	62.4	50.3	0.5	17
	Unshielded	62.4	41.6	9.0	17
18 mm	Shielded	64.5	50.9	0.5	24
	Unshielded	64.5	37.4	14	24
30 mm	Shielded	69.6	54.1	0.75	36
	Unshielded	69.6	35.8	19	36

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

iPROX™ INDUCTIVE PROXIMITY SENSORS

TYPE	MODEL NO.	PRICE	OPERATING VOLTAGE	SENSING RANGE (STD RANGE) mm	SHIELDING	CONNECTION TYPE m
2-WIRE SENSORS						
12 mm Dia NO Output	E59-M12A105C02-A1	£59.00	20 to 132 Vac 50/60 Hz	4	Shielded	2 cable
	E59-M12C110C02-A1	59.00		10	Unshielded	2 cable
18 mm Dia NO Output	E59-M18A109C02-A1	60.00		8	Shielded	2 cable
	E59-M18C118C02-A1	60.00		18	Unshielded	2 cable
30 mm Dia NO Output	E59-M30A115C02-A1	62.00		15	Shielded	2 cable
	E59-M30C129C02-A1	62.00		29	Unshielded	2 cable
3-WIRE SENSORS						
12 mm Dia NO Output	E59-M12A105C02-D1	£43.00	6 to 48 Vdc	4	Shielded	2 cable
	E59-M12C110C02-D1	43.00		10	Unshielded	2 cable
18 mm Dia NO Output	E59-M18A108C02-D1	65.00		8	Shielded	2 cable
	E59-M18C116C02-D1	47.50		18	Unshielded	2 cable
30 mm Dia NO Output	E59-M30A115C02-D1	53.00		29	Unshielded	2 cable
	E59-M30C129C02-D1	52.00		29	Unshielded	2 cable

Ordering Examples: E59-M18A109C02-A1, iProx sensor, 18 mm diameter, 8 mm sensing range, shielded with 2 m cable, £60.
 E59-M12A105C02-D1, iProx sensor, 12 mm diameter, 4 mm sensing range, shielded with 2 m cable, £43.

Accessories

MODEL NO.	PRICE	DESCRIPTION
E57KM12	£4.00	Bracket for 12 mm tubular sensors
E57KM18	4.00	Bracket for 18 mm tubular sensors
E58KAM18B	8.00	Bracket, adjustable ball swivel for 18 mm tubular sensors
E57KM30	4.70	Bracket for 30 mm tubular sensors



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters