

LDM35 Series

Signal Powered Limited Distance Modem



Model LDM35
\$104



The LDM35 Series of products is designed to allow video display terminals (VDTs) and other RS-232 devices to be connected over distances sufficient to cover any industrial or institutional complex of buildings. These modems feature a rugged enclosure small enough to mount on the back panel of VDT units, saving valuable desk and floor space.

The LDM35 Series does not require a power supply for operation. The use of low power circuits and a sensitive optical receiver allows the devices to derive all necessary power from the RS-232 data and control signal.


- ✓ Signal-Powered: No Power Source Required
- ✓ Optical Isolation: Breaks Ground Loops
- ✓ Heavy Duty Surge Protectors: Prevents Lightning Damage
- ✓ LED Diagnostic Indicators: Simplifies Installation and System Troubleshooting
- ✓ Operation to Two Miles (3.3 KM) at 9600 Baud, One-Half Mile (0.8 KM) at 19,200, Seven Miles (11.7 KM) at 1200 Baud
- ✓ Four-Wire Full Duplex, Two-Wire Simplex

- ✓ Selection of Connectors
- ✓ Wide Operating Temperature Range, 0 to 70°C
- ✓ Null Modem Switch

Specifications

Model	LDM35						
Baud Rate Range	0 – 19.2K						
Baud Rate	19.2K	9.6K	4.8K	2.4K	1.2K	.6K	.3K – 0
Distance (miles)	0.5	2	3	5	7	10	12
Distance (km)	0.8	3.3	5	8.3	11.7	16.7	20
Common Mode Isolation	500V Surge, 300V Continuous						
Differential Mode Surge Protection (3 devices)	ANSI/IEEE C37.90.1-1989						
Channel Lines ⁽¹⁾	TD, RD						
Control Lines ⁽¹⁾	RTS, CTS, DTR, DSR, RLSD						
Modes	Asynchronous 4-wire full duplex, 2-wire simplex						

Notes: (1) TD = Transmit Data, RD = Receive Data, RTS = Request To Send, CTS = Clear To Send, DTR = Data Terminal Ready, DSR = Data Set Ready, RLSD = Received Line Signal Detect.



They are designed for full-duplex, asynchronous operation over two, DC-continuity, non-loaded, twisted-wire pairs. Two-wire simplex operation may be accomplished over two wires. The modem circuits and, consequently, the host device are protected from electrical transients due to lightning strikes or operation of heavy industrial equipment.

Each device features a convenient Data-Communication Equipment (DCE) to Data-Terminal Equipment (DTE) switch which reverses pins 2 and 3 of the RS-232 connector. For installation and troubleshooting, each unit has diagnostic Light-Emitting Diodes (LEDs) on the transmit and receive lines.

The RS-232 connector may be ordered as a male or female 25-pin connector. Field connection is made through a modern, solderless, screw-termination assembly. Alternatively, a convenient four-wire modular phone jack is available.

Power Requirements

Model LDM35 is powered by the RS-232 data and control signals from its host computer or terminal device. It receives power from Data Terminal Ready, pin 20 or Request To Send, pin 4, and Transmitted

Data, pin 2. Transmitted data may be on pin 3 when the DCE/CTE switch is in the DTE position. For proper operation, minimum required signal voltage level is ± 6 V at 3.0 mA to 10.0 mA.

Model	LDM35
Power: RS-232 Data RS-232 Control Signals	RS-232 data and control signals, 3.0 mA to 10.0 mA ± 5 V to ± 15 V +6 V to +15 V, 3.0 mA to 10.0 mA
Operating Environment	0 to 70°C, 0 to 95% relative humidity, noncondensing
Dimensions	3.6 x 2.1 x 1.3" (91.4 x 53.3 x 25.4 mm)
Weight	90.1g (3.2 oz) max
MTBF⁽²⁾	>150,000 hrs

Notes: (2) Ground-benign environmental conditions (no salt atmosphere, <50°C ambient temperature).

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)			
Model No.	Price	RS232 Connector	Field Connector
LDM35-P	\$104	25 Pin male	Screw termination
LDM35-S	104	25 Pin female	Screw termination

Includes operator's manual.

Ordering Example: LDM35-S converter: \$104.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters