

OM-CP-SHOCK101 Tri-Axial Shock Data Logger

Part of the NOMAD Family

£401

Basic Unit



- ✓ Built-In Accelerometers
- ✓ Measures Dynamic and Static Acceleration
- ✓ Real-Time Operation
- ✓ Programmable Start Time
- ✓ Compact
- ✓ Reuseable

The OM-CP-SHOCK101 is a battery powered, stand alone temperature, pressure, humidity and 3-axis shock recorder.

The OM-CP-SHOCK101 measures and records temperature, pressure and humidity at the selected reading rates, while shock is recorded as the peak acceleration levels over the same interval.


The OM-CP-SHOCK101 is specifically designed for documenting dynamic environments such as moving vehicles, trucks, containers, ships, etc. The device is also valuable in characterizing environments such as production and assembly lines of delicate electronics, IC fabrication, communications and computer components. This compact, portable, easy to use device will measure and record up to 349,525 measurements per channel. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.

The OM-CP-SHOCK101 makes data retrieval quick and easy. Simply plug it into an empty COM or USB port and our user-friendly software does the rest. The Windows software converts your PC into a real time strip chart recorder. Data can be printed in graphical or tabular format and can also be exported to a text or Microsoft Excel file.

Specifications

Acceleration Type: MEMS semiconductor

Acceleration Range (g)	±5	±50	±100
Calibrated Accuracy (g)	±0.2	±1	±2
Acceleration Resolution (g)	0.01	0.05	0.1g



OM-CP-SHOCK101, £401, shown smaller than actual size

OM-CP-IFC110, £66, Windows software displays data in graphical or tabular format

Sampling Rate: 1.953 ms/512 Hz (note: data is sampled at this rate, only peak values are written at the end of a recording interval)
Frequency Response: 0 Hz to approx. 400 Hz
Memory: 349,525 readings per channel (1,398,100 total memory)
Recording Interval: 64 Hz to 5 minutes for shock, selectable through software
Real Time Recording: May be used with PC to monitor and record instantaneous acceleration in real time (1 sec or slower reading rate)
Start Modes: Immediate or delay start
Programmable Start Delay: Up to 180 days from PC launch
Password Protection: An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password
Calibration: Digital calibration through software

Calibration Date:

Automatically recorded within device
Power: 9V lithium or alkaline battery (included)
Battery Life: 3 to 7 days typical with lithium battery
Data Format: Date and time stamped, G and mG
Time Accuracy: ±1 minute per month at 20 to 30°C
Computer Interface: USB or serial interface (cable required) 115,200 baud
Software: Windows 95/98/NT/2000/XP/VISTA
Operating Environment: -20 to 60°C (-4 to 140°F)
 0 to 95% RH non-condensing
Dimensions: 89 H x 112 W x 26 mm D (3.5 x 4.4 x 1.0")
Weight: 340 g (12 oz)
Material: Anodized aluminum

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-SHOCK101-5	£401	Tri-axial shock data logger, ±5 g range
OM-CP-SHOCK101-50	401	Tri-axial shock data logger, ±50 g range
OM-CP-SHOCK101-100	401	Tri-axial shock data logger, ±100 g range
OM-CP-IFC110	66	Windows software and 1.2 m (4') RS-232 cable with DB9F termination
OM-CP-IFC200	80	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	14	Replacement 9V lithium battery

Operator's manual and RS-232 cable are included with the OM-CP-IFC110 Windows software and RS-232 cable (required to operate the data logger and sold separately).

Ordering Example: OM-CP-SHOCK101-5 tri-axial shock data logger and OM-CP-IFC110 Windows software and RS-232 cable.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters