


NON-METALLIC PUSHBUTTON ENCLOSURES

NEMA 4X (IP66) FOR 22 AND 30 MM PUSHBUTTONS



- Suited for Higher Temperatures or Corrosive Environments
- Protect Controls and Components Indoors or Outdoors
- 30 or 22 mm Hole Sizes
- UL 94 Flammability Rating
- UV Stabilized for Outdoor Use
- 304 SS Hardware and Continuous Hinge
- Optional Sub-Panels Available

OM-AMPB Series non-metallic fiberglass pushbutton enclosures are designed to insulate and protect electrical controls and components in both indoor and outdoor applications and are especially well suited for higher temperatures and corrosive environments. These NEMA 4X (IP66) fiberglass pushbutton enclosures feature stainless steel continuous hinge.

CONSTRUCTION

- Fiberglass Reinforced Polyester Formulation
- Closed Cell Neoprene Seal Designed for NEMA 4X (IP66) Rating
- 304 SS Continuous Hinge and Mounting Feet Included with SS Screws


SPECIFICATIONS

Service Temperature Rating:
-35 to 130°C (-31 to 266°F)

Standards: UL Types 1, 2, 3, 4, 4X, 12 and 13; CSA Types 1, 2, 3, 3R, 4 4X, 12 and 13; NEMA Types 1, 2, 3, 3R, 4, 4X, 12 and 13; IEC Type IP66

OM-AM1084HP9, 9 hole pushbutton enclosure,

All models shown smaller than actual size.



OM-AM1PB, 1 hole pushbutton enclosure.



OM-AM2PB, 2 hole pushbutton enclosure.



OM-AM3PB, 3 hole pushbutton enclosure.

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

| FLAT COVER SCREW CLOSURE MODELS | | | | | |
|---------------------------------|--------------------|--------|--------------|-------|--|
| MODEL NO. | NO. OF PUSHBUTTONS | HEIGHT | INCHES WIDTH | DEPTH | |
| OM-AM1PB | 1 | 6.75 | 4 | 3.63 | |
| OM-AM2PB | 2 | 6.75 | 4 | 3.63 | |
| OM-AM3PB | 3 | 9 | 4 | 3.63 | |
| OM-AM664HP4 | 4 | 6 | 6 | 4 | |
| OM-AM864HP6 | 6 | 8 | 6 | 4 | |
| OM-AM1084HP9 | 9 | 10 | 8 | 4 | |
| OM-AM1086HP9 | 9 | 10 | 8 | 6 | |
| OM-AM1086HP12 | 12 | 10 | 8 | 6 | |
| OM-AM1206HP16 | 16 | 12 | 10 | 6 | |
| OM-AM1206HP20 | 20 | 12 | 10 | 6 | |
| OM-AM1426HP25 | 25 | 14 | 12 | 6 | |
| OM-AM1648HP30 | 30 | 16 | 14 | 8 | |
| OM-AM1868HP42 | 42 | 18 | 16 | 8 | |

Accessories

| STEEL SUB-PANELS | DESCRIPTION |
|------------------|----------------------------------|
| SCE-6P6 | Sub-panel for 6 x 6" enclosure |
| SCE-8P6 | Sub-panel for 8 x 6" enclosure |
| SCE-10P8 | Sub-panel for 10 x 8" enclosure |
| SCE-12P10 | Sub-panel for 12 x 10" enclosure |
| SCE-14P12 | Sub-panel for 14 x 12" enclosure |
| SCE-16P14 | Sub-panel for 16 x 14" enclosure |
| OM-P186 | Sub-panel for 18 x 16" enclosure |

Note: For 22 mm button holes add "22" to the end of the model number, no additional cost. Mounting feet included on 4 button or larger models.

Ordering Examples: OM-AM3PB22, fiberglass pushbutton enclosure for 3, 22 mm pushbuttons, 9 H x 4 W x 3.63" D E

OM-AM1086HP9, fiberglass pushbutton enclosure for 9, 30 mm pushbuttons, mounting feet included, 10 H x 8 W x 6" D E

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters