



NORGREN EXCELON® PRESSURE RELIEF VALVES

V72G Series
Starts at
\$50



- In-Line or Modular Installation
- Push to Lock Adjusting Knob with Tamper Resistant Accessory
- Helps Protect Air Operated Equipment from Over Pressure by Retarding Excessive Pressure Build Up

SPECIFICATIONS

Fluid: Compressed air

Maximum Pressure: 20 bar (300 psig)

Operating Temperature*:
-34 to 65°C (-30 to 150°F)

MATERIALS

V72:

Gage Port: 1/8" PTF with PTF main ports; 1/8" ISO Rc with ISO G main ports

Exhaust Port: 1/4" PTF with PTF main ports; 1/4" ISO Rc with ISO G main ports



V72G-2AK-NMG, \$50, shown smaller than actual size.

V72G:

Body: Zinc
Bonnet: Acetal
Elastomers: Neoprene
Bottom Plug: Acetal



V74G-3AK-NMG, \$78, shown smaller than actual size.

V74G:

Body and Bonnet: Aluminum
Valve: Aluminum and nitrile
Elastomers: Nitrile
Bottom Plug: Acetal

* Air supply must be dry enough to avoid ice formation at temperatures below 2°C (35°F).

OPTIONS SELECTOR

V7 □ G - □ □ □ - N □ □

Series	Substitute
72	2
74	4

Port size	Substitute
1/4" (72)	2
3/8" (72, 74)	3
1/2" (74)	4
3/4" (74)	6

Threads	Substitute
PTF	A
ISO G parallel	G

Gage	Substitute
With	G
Without	N





Relief pressure adjustment range*	Substitute
0.3 to 4 bar (5 to 60 psig)	F
0.3 to 10 bar (5 to 150 psig)	M
0.7 to 17 bar (10 to 250 psig)	S

Adjustment	Substitute
Knob	K
T-bar	T

* Relief valve can be adjusted to pressures in excess of, and less than, those specified. Do not use these units to control pressures outside of the specified ranges.

** Units with 250 psig relief pressure range are available only with the T-bar adjustment; therefore substitute T at the 7th position and S at the 9th position.

TYPICAL PERFORMANCE CHARACTERISTICS



STANDARD DIMENSIONS (in)								
SERIES	A	B	C	F	G	H	PANEL DIA.	PANEL DEPTH
72	2.87	0.98	1.02	1.97	1.89	1.38	1.57	0 to 0.2
74	5.00	1.69	1.22	3.15	2.91	2.20	2.05	0.08 to 0.2
METRIC DIMENSIONS (mm)								
72	28.3	26.4	26.4	27.4	27.3	26.8	27.0	0 to 5
74	30.4	27.1	26.6	28.6	28.3	27.6	27.5	2 to 5

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	PORT SIZE (in)	PRESSURE RANGE
V72G-2AK-NMG	\$50	1/4	0.3 to 10 bar (5 to 150 psig)
V72G-3AK-NMG	52	3/8	0.3 to 10 bar (5 to 150 psig)
V74G-3AK-NMG	78	3/8	0.3 to 10 bar (5 to 150 psig)
V74G-4AK-NMG	78	1/2	0.3 to 10 bar (5 to 150 psig)
V72G-2AK-NFG	55	1/4	0.3 to 4 bar (5 to 60 psig)

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
OM-AIR-4224-50	\$7.00	Wall mounting bracket for V72G model
OM-AIR-4324-50	9.25	Wall mounting bracket for V74G model
OM-AIR-74316-50	7.00	Neck mounting bracket for V72G model
OM-AIR-4368-51	13.50	Neck mounting bracket for V74G model

Notes: For Excelon® 73 combinations use V74G

Ordering Examples: V72G-2AK-NMG, pressure relief valve with 1/4" port, PTF threads, 5 to 150 psig adjustment range, with pressure gage, \$50.

V74G-3AK-NMG, pressure relief valve with 3/8" port, PTF threads, 5 to 150 psig adjustment range, with pressure gage, \$78.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters